



● 材質・仕上げ

 RoHS2適合

	VME
本体	ガラス繊維強化ナイロン66
ベアリング	スチール ゴムシール

品番 	価格 (円)	アイドラー											ベアリング			質量 (kg)	適用アイドラー軸
		溝形状	De	Da	Db	W	w1	s2	θ(°)	r	h	呼び番号	d	D	B		標準アイドラー軸  → P.xxxx
VME63A1-6200	630	A1	63	27	36	19	12	5	34	2	12.5	6200×1	10	30	9	0.06	Z6200 - 15・Z6200 - 20
VME63M1-6200	810	M1	63	27	36	15	9.7	3	34	1	9	6200×1	10	30	9	0.07	Z6200 - 10・Z6200 - 15・Z6200 - 20
VME70A1-6202	750	A1	70	32	41	19	12	4	34	1	12.5	6202×1	15	35	11	0.09	Z6202 - 16・Z6202 - 22
VME80B1-6202	780	B1	80	32	41	21	16	5	35	4.5	15	6202×1	15	35	11	0.10	Z6202 - 16・Z6202 - 22
VME85B1-6203	870	B1	85	37	46	22	15.9	5	34	1	15	6203×1	17	40	12	0.12	Z6203 - 15・Z6203 - 20
VME120B1-6202	1,510	B1	120	32	41	22	15.9	5.5	34	1	15	6202×1	15	35	11	0.16	Z6202 - 16・Z6202 - 22

● 品番指定


VME63M1-6200

 軸穴・キー溝・押しねじ追加工 → P.xxxx

対応不可