



● Material/Finish RoHS Compliant

	GGB
Grip Part	EPDM (Matte Black)
Thread Part	SS400 Chrome Plating

Part Number	D	M	Lm	d	d1	H	e	B	h	Mass (g)	Unit : mm
GGB-6	28	M6	13	14	10	45.5	8	8	37.5	25	
GGB-8	35.5	M8	15	17.8	13	56.5	9	10	47.5	40	
GGB-10	45	M10	18	22.5	16	72	12	14	60	85	

● Related Products

KGB

Rubber ball-shaped knob is available.

➔ P.314



● Part number specification

GGB-6



Cleanroom Wash & Packaging ➔ P.792 Not Available	Vibration Resistant ➔ P.795 Available / Add'l charge	Laser Marking ➔ P.806 Not Available	Modification of Shaft Hole Diameter ➔ P.800 Not Available
---	---	--	--