

# F2

## Flange Fitting Flexible Hose



### NK-2500

(Floating x Fixed Flange)

### NK-2600

(Both Ends Floating Flange)

Wide Use Type

DN: 10mm(3/8") ~ 350mm(14")

Length: 200mm ~ 10M

\*For any other specifications, please contact us.

Flange Standard: JIS, ANSI, DIN, ASME

① Tube	Stainless Steel
② Braid	Stainless Steel
③ Ring	Stainless Steel
④ Stub End	Carbon Steel, Stainless Steel
⑤ Flange	Carbon Steel, Stainless Steel
⑥ End Pipe	Carbon Steel, Stainless Steel



NK-2500



NK-2600

### NK-3100

Standard Type

DN: 15mm(1/2") ~ 250mm(10")

Length: 150mm ~ 3M

\*For any other specifications, please contact us.

Flange Standard: JIS, ANSI, DIN, ASME

① Tube	Stainless Steel
② Braid	Stainless Steel
③ Collar	Stainless Steel
④ Flange	Carbon Steel, Stainless Steel

