

# F4

## Quick Connection Flexible Hose



### NK-1800 Sanitary Flange Type

DN: 10mm(3/8") ~ 300mm(12") 1.0S ~ 6.0S(STD type), 1.0S ~ 2.0S(SNT type)  
 Length: 200mm ~ 3M \*For any other specifications, please contact us.

- ① NK-1800STD Normal Type
- ② NK-1800SNT Flat End Type

① <b>Tube</b>	Stainless Steel
② <b>Braid</b>	Stainless Steel
③ <b>Ring</b>	Stainless Steel
④ <b>Sanitary Flange</b>	Stainless Steel



### NK-3500 Lever Coupling Type

DN: 15mm(1/2") ~ 200mm(8")  
 Length: 500mm ~ 10M \*For any other specifications, please contact us.

① <b>Tube</b>	Stainless Steel
② <b>Braid</b>	Stainless Steel
③ <b>Ring</b>	Stainless Steel
④ <b>Nipple</b>	Carbon Steel, Stainless Steel
⑤ <b>Coupling</b>	Carbon Steel, Stainless Steel, Copper Alloy
⑥ <b>Plug</b>	Carbon Steel, Stainless Steel, Copper Alloy
⑦ <b>Gasket</b>	Non Asbestos



### NK-3600 Coupler Type

DN: 15mm(1/2") ~ 200mm(8")  
 Length: 500mm ~ 10M \*For any other specifications, please contact us.

① <b>Tube</b>	Stainless Steel
② <b>Braid</b>	Stainless Steel
③ <b>Ring</b>	Stainless Steel
④ <b>Nipple</b>	Carbon Steel, Stainless Steel
⑤ <b>Socket</b>	Carbon Steel, Stainless Steel, Copper Alloy
⑥ <b>Plug</b>	Carbon Steel, Stainless Steel, Copper Alloy
⑦ <b>Packing</b>	Non Asbestos



Threaded Type Flexible Hose

F1

Flange Type Flexible Hose

F2

Fire Law Flexible Hose

F3

Quick Connection Flexible Hose

F4

Flexible Hose for Vacuums

F5

Flexible Hose with Fluororesin

F6

Other Flexible Hose

F7