

USE

- Measurement of gap width

MATERIAL

- SFG series : Stainless steel
- FG series : Carbon tool steel (Hardened)

FEATURES

- Use for assembly or adjustment of automotive engine components or other machines by cutting it to necessary size
- Leaf width: 12.7mm
- 3m and 5m also available



SFG series (Stainless Steel)

Order No.	Model No.	Size	Leaf Width (mm)	Accuracy (mm)	Case size (mm)	Weight
007245	SFG-005-1	0.005 × 1m	12.7	±0.004	77×77×22	40g
007251	SFG-01-1	0.01 × 1m				
007252	SFG-02-1	0.02 × 1m				
007381	SFG-03-1	0.03 × 1m				
007382	SFG-04-1	0.04 × 1m				
007383	SFG-05-1	0.05 × 1m		±0.005		
007384	SFG-06-1	0.06 × 1m				
007385	SFG-07-1	0.07 × 1m				
007386	SFG-08-1	0.08 × 1m				
007387	SFG-09-1	0.09 × 1m				
007388	SFG-10-1	0.10 × 1m	±0.006	50g		

FG series (Carbon Tool Steel)

Order No.	Model No.	Size	Leaf Width (mm)	Accuracy (mm)	Case size (mm)	Weight
007253	FG-03-1	0.03 × 1m	12.7	±0.005	77×77×22	40g
007254	FG-04-1	0.04 × 1m				
007255	FG-05-1	0.05 × 1m				
007256	FG-06-1	0.06 × 1m				
007257	FG-07-1	0.07 × 1m				
007258	FG-08-1	0.08 × 1m		±0.01		
007259	FG-09-1	0.09 × 1m				
007260	FG-10-1	0.10 × 1m				
007261	FG-11-1	0.11 × 1m				
007262	FG-12-1	0.12 × 1m				
007263	FG-13-1	0.13 × 1m	±0.012	115×115×22	50g	
007264	FG-14-1	0.14 × 1m				
007265	FG-15-1	0.15 × 1m				
007270	FG-20-1	0.20 × 1m				
007275	FG-25-1	0.25 × 1m				
007280	FG-30-1	0.30 × 1m	±0.02	-	60g	
007282	FG-35-1	0.35 × 1m				
007284	FG-40-1	0.40 × 1m				
007286	FG-45-1	0.45 × 1m				
007287	FG-50-1	0.50 × 1m				
007289	FG-60-1	0.60 × 1m	±0.02	-	60g	
007291	FG-70-1	0.70 × 1m				
007292	FG-80-1	0.80 × 1m				
007293	FG-90-1	0.90 × 1m				
007294	FG-00-1	1.00 × 1m				

BLOCK GAUGES

PIN GAUGES

PIN VISE

PIN GAUGE ACCESSORIES

GAUGES

THREAD GAUGES

PLUG GAUGES

RING GAUGES

THICKNESS GAUGES

TAPER GAUGES

WELDING GAUGES

OTHER GAUGES