



CNS Grinders

- Ideal for fine finish work and removal of black scale, oxide layer, or paint.

Safety Grip Type



NHG-75G

Model	Code	Wheel size		Max.free speed min ⁻¹	Overall length		Height		Weight		Max. output		Airinlet thread Rc or NPT	Hose size		Average air consumption	
		mm	in		mm	in	mm	in	kg	lb	kw	ps		mm	in	m ³ /min	ft ³ /min
NHG-75G	10074	100x26x9.5	4 x 1/4 x 5/8	6000	328	12 15/16	-	-	1.7	3.7	0.77	1.05	1/4	9.5	3/8	0.45	15.9

Options CNS Wheel





Wheel for NHG-75G (Disk Type)
 Max 6000 RPM : 6000(r.p.m)
 Wheel Size : 100x13(mm)
 Code : No.24906003



Wire Brush Sanders

- Ideal for removing rust and paint, and descaling beads after welding.

Safety Grip Type

Safety Lever Type



NAG-70WA



NAG-70WALW

Model	Code	Wheel size		Max.free speed min ⁻¹	Overall length		Height		Weight		Max. output		Airinlet thread Rc	Hose size		Average air consumption	
		mm	in		mm	in	mm	in	kg	lb	kw	hp		mm	in	m ³ /min	cfm
NAG-70WA	10744	120x22	4 3/4 x 7/8	6500	257	10 1/8	109	4 5/16	2.8	6.2	1.2	1.6	3/8	12.7	1/2	0.9	31.8
NAG-70WALW	10714	120x22	4 3/4 x 7/8	6500	276	10 7/8	109	4 5/16	2.8	6.2	1.2	1.6	3/8	12.7	1/2	0.9	31.8