

AC Free Input Axial Fans

Common
Product list

AC Free Input Axial Fan

DC Axial Fan

AC Axial Fan
Plastic blade

AC Axial Fan
Metal blade

Accessories

Box Fan

Attachment / Filter

Series	Size (mm)	Model	Power supply voltage (V)	Rotational speed	Safety standards			Terminal type	Page	
					Compliant standards		Certified standards			
					CE mark	UL				CSA
R89F Fans with Plastic Blades	 92 × 92 × t38	R89F-MS0938HP	100 to 240 VAC	High	Yes	Yes	Yes	Terminals only	20	
		R89F-MS0938LP	100 to 240 VAC	Low	Yes	Yes	Yes	Terminals only		
	 120 × 120 × t38	R89F-MS1238HP	100 to 240 VAC	High	Yes	Yes	Yes	Terminals only	21	
Plug Cords		R89F-PC-□	---	---	---	Yes	---	---	50	
Finger Guards		R87F-FG□			---	---	---		---	52
Filters		R87F-FL□(S)			---	---	---		---	53