




DC Axial Fans

Series	Size (mm)	Model	Power supply voltage (V)	Rotational speed	Safety standards			Terminal type	Page
					Compliant standards		Certified standards		
					CE mark	UL			
R89F Fans with Plastic Blades	 92 × 92 × t25	R89F-DS0925H	24 VDC	High	Yes	Yes	Yes	Lead wires only	23
		R89F-DS0925L	24 VDC	Low	Yes	Yes	Yes	Lead wires only	
	 120 × 120 × t25	R89F-DS1225H	24 VDC	High	Yes	Yes	Yes	Lead wires only	24
		R89F-DS1225L	24 VDC	Low	Yes	Yes	Yes	Lead wires only	
	 120 × 120 × t38	R89F-DS1238H	24 VDC	High	Yes	Yes	Yes	Lead wires only	25
		R89F-DS1238L	24 VDC	Low	Yes	Yes	Yes	Lead wires only	
Finger Guards		R87F-FG□		---	---	---	---	---	52
Filters		R87F-FL□(S)		---	---	---	---	---	53

Common Product list

AC Free Input Axial Fan

DC Axial Fan

AC Axial Fan Plastic blade

AC Axial Fan Metal blade

Accessories

Box Fan

Attachment / Filter