

# 貫通端子台 Through type

貫通端子台 (250V-600V) Through type (for 250V-600V)



【例】 OGM-300  
11 × □P + 19.4











【例】 OTB-6223  
11 × □P ÷ 2 + 9












(A) : 幅を表示  
(B) : 高さを表示  
(C) : 端子間ピッチ

	(A) 18 (B) 16.8  ワンタッチカバー (オプション)	(A) 18 (B) 16.8  ワンタッチカバー (オプション)	(A) 18 (B) 15.5  板カバー、LCカバー (オプション)	(A) 23.5 (B) 28  板カバー (オプション)
品番 Part Number	<b>OGM-300F</b> <b>OGM-300F-1 (アルミ材)</b>	<b>OGM-300</b>	<b>OGM-300NE</b>	<b>OTB-6223</b>
定格 Rating	300V - 25A	300V - 25A	300V - 25A	250V - 10A
全長 Length	(C) 11 × P + 19.4	(C) 11 × P + 19.4	(C) 11 × P + 19	(C) 11 × P ÷ 2 + 9
極数 Pole	2 - 12	2-6、⑦、8、⑨、10、⑪、12 (○印特注品)	2-6、⑦、8、⑨、10、⑪、⑫、⑬、14-16、⑰-⑲ (○印特注品)	3 - 45
ビスサイズ Screw Size / type	M 4	M 4	M 4	M 4
認定 Authorized Standard	 (FW2) 	 (FW2) 	 (FW2)  TUV	 (FW2)

	(A) 19 (B) 18  板カバー (オプション)	(A) 18 (B) 14  ハンダ付けが簡単 ワンタッチカバー (オプション)	(A) 18 (B) 14  板カバー (オプション)	(A) 18 (B) 14  板カバー (オプション)
品番 Part Number	<b>OTB-167N-M</b>	<b>OTB-306NS</b> PAT	<b>OTB-306N</b>	<b>OTB-307N</b>
定格 Rating	250V - 15A	300V - 20A	250V - 20A	250V - 20A
全長 Length	(C) 11 × P + 20	(C) 11 × P + 20	(C) 11 × P + 20	(C) 11 × P + 20
極数 Pole	2 - 20	2-6、⑦、8、⑨、10 (○印特注品)	2 - 22	2-6、⑦、8、⑨、10、⑪、12-15、⑰-⑲ (○印特注品)
ビスサイズ Screw Size / type	M 4	M 4	M 4	上 M 4、下 M 3 (上下 M 3 特注品)
認定 Authorized Standard	 (FW2)	 (FW2) 	 (FW2) 	 (FW2) 

	(A) 20 (B) 17  ワンタッチカバー (オプション)	(A) 24 (B) 24  ワンタッチカバーオプション (LOCカバー可)	(A) 24 (B) 24  ワンタッチカバー (オプション)	(A) 24 (B) 38  板カバー (オプション)
品番 Part Number	<b>OTB-150</b>	<b>OTB-3013N</b>	<b>OTB-3013NS</b>	<b>OTB-3013</b>
定格 Rating	300V - 30A	 600V-50A / TUV 1000V-50A	300V - 50A	600V - 40A
全長 Length	(C) 12 × P + 22	(C) 13 × P + 23	(C) 13 × P + 23	(C) 13 × P + 23
極数 Pole	2 - 15	2-6、⑦、8、⑨、10 (○印特注品)	2 - 10	2-6、⑦、8、⑨、10、⑪、12 (○印特注品)
ビスサイズ Screw Size / type	M 4	M 4, M 5	M 5	M 4
認定 Authorized Standard	 (FW2)	 (FW2) TUV	 (FW2)	 (FW2) 

	(A) 30 (B) 25  ワンタッチカバー付き (添付)	(A) 24 (B) 23  ワンタッチカバーオプション (LOCカバー可)	(A) 24 (B) 25  ワンタッチカバー付き (添付)	(A) 25 (B) 43  ワンタッチカバー (オプション・上/下あり)
品番 Part Number	<b>OTB-591</b> PAT	<b>OTB-3013UH</b> PAT	<b>OTB-330N-□P-7B</b>	<b>OTB-350</b>
定格 Rating	600V - 50A	600V - 50A	600V - 50A	600V - 90A
全長 Length	(C) 13 × P + 23.6	(C) 13 × P + 23	(C) 13 × P + 24	(C) 14.5 × P + 26
極数 Pole	2 - 10	②、3、4、⑤、6、⑦、8、⑨、⑩ (○印特注品)	2 - 15	1 - 12
ビスサイズ Screw Size / type	M 4, M 5 (特注品)	M 5	M 4	M 5
認定 Authorized Standard	 (FW2)	 (FW2)	 (FW2)	 (FW2)  (申請中)

カバー付き/カバー (オプション) は添付となります。