



表3：LFM, MLFMシリーズ寸法表

スタンダード		主要寸法 (mm)										玉列数	質量 (kg)	基本定格荷重	
標準型 両シール付	防錆型 両シール付	d	D		L	フランジ				C (N)	Co (N)				
LFM6-UU	MLFM6-UU	6	0 -0.009	12	0 -0.021	19	28	5	20	M3	4	0.023	218	160	
LFM8-UU	MLFM8-UU	8		15		24	32	5	24	M3	4	0.037	258	220	
LFM10-UU	MLFM10-UU	10		19		29	39	6	29	M4	4	0.061	532	430	
LFM12-UU	MLFM12-UU	12		21		30	42	6	32	M4	4	0.070	549	430	
LFM13-UU	MLFM13-UU	13		23		32	43	6	33	M4	4	0.080	555	440	
LFM16-UU	MLFM16-UU	16		28		37	48	6	38	M4	5	0.109	768	650	
LFM20-UU	MLFM20-UU	20	0 -0.010	32	0 -0.025	42	54	8	43	M5	5	0.176	1282	1010	
LFM25-UU	MLFM25-UU	25		40		58	62	8	51	M5	6	0.300	2164	1790	
LFM30-UU	MLFM30-UU	30		45		64	74	10	60	M6	6	0.43	3245	2510	
LFM35-UU	MLFM35-UU	35	0 -0.012	52	0 -0.030	70	82	10	67	M6	6	0.59	3521	3090	
LFM40-UU	MLFM40-UU	40		60		80	96	13	78	M8	6	1.21	4844	4040	
LFM50-UU	MLFM50-UU	50		80		100	116	13	98	M8	6	1.99	8272	6430	
LFM60-UU	MLFM60-UU	60	0 -0.015	90	0 -0.035	110	134	18	112	M10	6	3.20	9847	7270	

