

# UK 2,5 N - Feed-through terminal block

3003347

<https://www.phoenixcontact.com/pc/products/3003347>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Feed-through terminal block, nom. voltage: 800 V, nominal current: 24 A, number of connections: 2, connection method: Screw connection, Rated cross section: 2.5 mm<sup>2</sup>, cross section: 0.2 mm<sup>2</sup> - 4 mm<sup>2</sup>, mounting type: NS 35/7,5, NS 35/15, NS 32, color: gray

## Your advantages

- Universal foot which can be used on NS 35... and NS 32... DIN rails
- The UK universal screw terminal block series has the typical features which are decisive for practical applications
- Potential distribution via fixed bridges in the terminal center or insertion bridges in the clamping space

## Commercial data

Item number	3003347
Packing unit	50 pc
Minimum order quantity	50 pc
Product key	BE1211
Catalog page	Page 459 (C-1-2019)
GTIN	4017918099299
Weight per piece (including packing)	6.36 g
Weight per piece (excluding packing)	5.7 g
Customs tariff number	85369010
Country of origin	IN