

UNFサイズ部品番号及び寸法

サイズ		MS規格						
径	長さ	Part.No.	自由外径 最小最大	自由巻数	フリー Part.No.	ロック Part.No.	自由外径 最小最大	自由巻数
#3-56	1D	04532	3.15 3.25	3.600	04532MS	14532	3.32 3.70	3.375
	1.5D	04533		6.050	04533MS	14533		5.625
	2D	04534		8.650	04534MS	14534		8.000
	2.5D	04535		11.250	04535MS			10.375
	3D	04536		13.750	04536MS			12.625
#4-48	1D	04542	3.57 3.67	3.550	04542MS	14542	3.73 4.11	3.375
	1.5D	04543		5.950	04543MS	14543		5.625
	2D	04544		8.250	04544MS	14544		7.875
	2.5D	04545		10.950	04545MS			10.250
	3D	04546		13.350	04546MS			12.500
#6-40	1D	04562	4.38 4.50	3.550	04562MS	14562	4.39 4.90	3.500
	1.5D	04563		6.150	04563MS	14563		6.000
	2D	04564		8.650	04564MS	14564		8.375
	2.5D	04565		11.150	04565MS			10.750
	3D	04566		13.750	04566MS			13.250
#8-36	1D	04582	5.14 5.28	3.850	04582MS	14582	5.18 5.68	3.875
	1.5D	04583		6.850	04583MS	14583		6.500
	2D	04584		9.350	04584MS	14584		9.125
	2.5D	04585		11.950	04585MS			11.625
	3D	04586		14.650	04586MS			14.250
#10-32	1D	04602	5.85 6.00	4.250	04602MS	14602	5.99 6.50	4.125
	1.5D	04603		7.050	04603MS	14603		6.875
	2D	04604		9.950	04604MS	14604		9.500
	2.5D	04605		12.250	04605MS	14605		12.000
	3D	04606		15.650	04606MS	14606		14.875
#12-28	1D	04622	6.73 7.18	4.250	04622MS	14622	6.73 7.18	4.250
	1.5D	04623		7.300	04623MS	14623		7.300
	2D	04624		9.850	04624MS	14624		9.850
1/4-28	1D	04042	7.60 7.80	5.050	04042MS	14042	9.14 8.28	5.000
	1.5D	04043		8.450	04043MS	14043		8.250
	2D	04044		11.650	04044MS	14044		11.375
	2.5D	04045		14.950	04045MS	14045		14.500
	3D	04046		18.150	04046MS	14046		17.625
5/16-24	1D	04052	9.45 9.65	5.550	04052MS	14052	9.65 10.16	5.500
	1.5D	04053		9.050	04053MS	14053		8.875
	2D	04054		12.550	04054MS	14054		12.250
	2.5D	04055		16.150	04055MS	14055		15.625
	3D	04056		19.650	04056MS	14056		19.000
3/8-24	1D	04062	11.00 11.20	7.050	04062MS	14062	11.37 11.88	6.875
	1.5D	04063		11.250	04063MS	14063		11.000
	2D	04064		15.450	04064MS	14064		15.000
	2.5D	04065		19.750	04065MS	14065		19.125
	3D	04066		23.450	04066MS	14066		23.125
7/16-20	1D	04072	12.96 13.20	6.850	04072MS	14072	13.30 13.94	6.625
	1.5D	04073		11.050	04073MS	14073		10.625
	2D	04074		15.250	04074MS	14074		14.625
	2.5D	04075		19.750	04075MS	14075		18.500
	3D	04076		23.450	04076MS	14076		22.500
1/2-20	1D	04082	14.60 14.90	8.050	04082MS	14082	15.03 15.67	7.875
	1.5D	04083		12.750	04083MS	14083		12.375
	2D	04084		17.450	04084MS	14084		16.875
	2.5D	04085		22.050	04085MS	14085		21.375
	3D	04086		26.750	04086MS	14086		25.875
9/16-18	1D	04092	16.38 16.68	8.150	04092MS	14092	16.91 17.55	8.000
	1.5D	04093		12.850	04093MS	14093		12.500
	2D	04094		17.650	04094MS	14094		17.125
	2.5D	04095		22.450	04095MS	14095		21.750
	3D	04096		27.150	04096MS	14096		26.250

サイズ		MS規格						
径	長さ	Part.No.	自由外径 最小最大	自由巻数	フリー Part.No.	ロック Part.No.	自由外径 最小最大	自由巻数
5/8-18	1D	04102	18.00 18.30	9.250	04102MS	14102	18.61 19.25	9.000
	1.5D	04103		14.550	04103MS	14103		14.125
	2D	04104		20.050	04104MS	14104		19.250
	2.5D	04105		25.050	04105MS	14105		24.250
	3D	04106		30.450	04106MS	14106		29.375
3/4-16	1D	04122	21.20 21.60	9.950	04122MS	14122	22.25 22.88	9.750
	1.5D	04123		15.550	04123MS	14123		15.125
	2D	04124		21.350	04124MS	14124		20.625
	2.5D	04125		26.850	04125MS	14125		26.000
	3D	04126		32.650	04126MS	14126		31.500
7/8-14	1D	04142	24.97 25.33	10.150	04142MS	14142	25.93 26.69	9.875
	1.5D	04143		16.150	04143MS	14143		15.500
	2D	04144		22.050	04144MS	14144		21.125
	2.5D	04145		27.850	04145MS	14145		26.625
	3D	04146		33.750	04146MS	14146		32.250
1"-12	1D	04162	28.47 28.83	9.950	04162MS	14162	29.69 30.45	9.625
	1.5D	04163		15.350	04163MS	14163		15.000
	2D	04164		21.350	04164MS	14164		20.500
	2.5D	04165		27.150	04165MS	14165		26.000
	3D	04166		32.950	04166MS	14166		31.500
1"-14	1D	04162-14	28.07 28.43	11.950	04162-14MS	14162-14	29.36 30.12	11.500
	1.5D	04163-14		18.550	04163-14MS	14163-14		17.875
	2D	04164-14		25.050	04164-14MS	14164-14		24.250
	2.5D	04165-14		31.750	04165-14MS	14165-14		30.625
	3D	04166-14		38.350	04166-14MS	14166-14		37.000
1-1/8-12	1D	04182	31.72 32.10	11.550	04182MS	14182	33.12 33.88	11.125
	1.5D	04183		17.950	04183MS	14183		17.250
	2D	04184		24.350	04184MS	14184		23.375
	2.5D	04185		30.850	04185MS	14185		29.500
	3D	04186		37.350	04186MS	14186		35.750
1-1/4-12	1D	04202	34.90 35.30	12.950	04202MS	14202	36.55 37.31	12.500
	1.5D	04203		20.150	04203MS	14203		19.375
	2D	04204		27.450	04204MS	14204		26.250
	2.5D	04205		34.550	04205MS	14205		33.000
	3D	04206		41.750	04206MS	14206		39.875
1-3/8-12	1D	04222	38.22 38.52	14.250	04222MS	14222	40.00 40.89	13.750
	1.5D	04223		22.250	04223MS	14223		21.375
	2D	04224		30.150	04224MS	14224		28.875
	2.5D	04225		38.150	04225MS	14225		36.500
	3D	04226		46.050	04226MS	14226		44.000
1-1/2-12	1D	04242	41.38 41.78	15.850	04242MS	14242	43.43 44.32	15.250
	1.5D	04243		24.550	04243MS	14243		23.500
	2D	04244		33.050	04244MS	14244		31.625
	2.5D	04245		41.750	04245MS	14245		39.875
	3D	04246		50.350	04246MS	14246		48.125

1.5D = インサートの呼び径の1.5倍

