



寸法表

(mm)

呼び (鋼管)		LA 型			HI-LA マルチ・(P-LA 型)			
		L	I	E	L	I	C	d(Rc)
$\frac{3}{8} \times \frac{1}{2}$	10 × 15	55	48	25	60 (60)	48	25	$\frac{1}{2}$
$\frac{1}{2}$	15	57	50	27	63 (62)	50	27	$\frac{1}{2}$
$\frac{3}{4}$	20	61	53	30	66 (65)	53	30	$\frac{3}{4}$
1	25	66	58	35	72 (71)	58	35	1
$1\frac{1}{4}$	32	70	62	34	77 (75)	62	34	$1\frac{1}{4}$
$1\frac{1}{2}$	40	73	64	35	82 (78)	64	35	$1\frac{1}{2}$
2	50	81	72	42	91 (86)	72	42	2
$2\frac{1}{2}$	65	91	81	41	101 (99)	81	41	$2\frac{1}{2}$
3	80	94	83	44	104 (102)	83	44	3



径違いソケット (RS)			
呼び (鋼管)	HI-LA マルチ		
B	L	A	E
$\frac{1}{2} \times \frac{3}{8}$	81	55	9



● F-LA 型

ソケット (F-LA-S)							
呼び (鋼管)	F-LA 型						
B	A	L	I	E	フランジ 最大寸法 (W)	ボルト 呼び	ボルト 本数
4	100	200	160	16	229	M16	4
5	125	226	180	20	262	M16	6
6	150	262	210	32	301	M20	6

