

Keys (mm/Torx) sizes




Ordering code	Key		
	(mm)	(inch)	(Torx Plus)
170.3-860	2.5	-	-
174.1-864	3	-	-
265.2-817	3	-	-
265.2-821	4	-	-
3021 010-025	2.5	-	-
3021 010-030	3	-	-
3021 010-040	4	-	-
3021 010-050	5	-	-
3021 010-060	6	-	-
3021 010-080	8	-	-
3021 011-764	-	7/64	-
3021 012-020	2	-	-
3021 013-100	10	-	-
3021 013-120	12	-	-
5680 049-01	3.5	-	15IP
5680 049-02	4	-	15IP
5680 049-04	3.5	-	10IP
5680 051-02	-	-	07IP
5680 051-03	-	-	09IP

Ordering code	Screwdriver	
	(mm)	(Torx Plus)
5680 046-01	-	08IP
5680 046-02	-	15IP
5680 046-03	-	07IP
5680 046-04	-	09IP
5680 046-05	-	10IP

5680 100

5680 099



Ordering code	Torque wrench		
	(mm)	(Torx Plus)	Torque value Nm (in-lbs)
5680 099-01	5	-	3-15 (27 -133)
5680 100-05	-	10IP	2.0 (18)
Torque key			
5680 073-01	-	06IP	0.5



Ordering code	Bit		Torque wrench	
	(mm)	(Torx Plus)	Ordering code	Torque value Nm
5680 083-01	3	-	C-TK-01	20-100
5680 084-03	-	15IP	C-TK-02	40-200
5680 084-08	-	20IP		



Ordering code	(mm)	(Torx Plus)	Length	
			(mm)	(inch)
5680 015-01	10		190	7.480
5680 015-02	14		200	7.874
5680 015-03	10		238	9.370
5680 015-04	14		260	10.236
5680 015-05	8		163	6.417
5680 015-07	8		245	9.646
5680 035-06	10		60	2.362
5680 035-07	12		60	2.362
5680 035-15		40IP	73	2.874