


Cylindrical shank to CoroTurn® SL dampened adaptor



● ● ● ● ● SilentTools®

Metric version

							Dimensions									
CZC _{MS}	CZC _{WS}	OHN	OHX	CNSC	CXSC	Ordering code	DCON _{MS}	DCON _{WS}	LPR	LF	WF	HF	CNT	CP BarPSI	Kg	
16	16	55	92	1	3	570-3C 16 156	16	16	156	156	0	0	G1/8"	70	0.2	
20	20	70	120	1	3	570-3C 20 200	20	20	200	200	0	0	G1/4"	70	0.4	
25	25	88	158	1	3	570-3C 25 255	25	25	255	255	0	0	G1/4"	70	1.0	
	25	155	230	1	3	570-3C 25 330	25	25	330	330	0	0	G1/4"	70	1.2	
	25	88	158	1	1	SL-3C 25 255	25	25	255	255	0	0	G 1/4"	70	0.9	
32	25	155	230	1	1	SL-3C 25 330	25	25	330	330	0	0	G 1/4"	70	1.3	
	32	100	192	1	1	570-3C 32 320	32	32	320	320	0	0	G3/8"	70	2.1	
40	32	192	288	1	1	570-3C 32 416	32	32	416	416	0	0	G3/8"	70	2.9	
	40	128	248	1	1	570-3C 40 408	40	40	408	408	0	0	G1/2"	70	4.6	
50	40	248	368	1	1	570-3C 40 528	40	40	528	528	0	0	G1/2"	70	15.3	
	50	165	310	1	1	570-3C 50 510	50	50	510	510	0	0	G1/2"	70	15.4	
60	50	310	460	1	1	570-3C 50 660	50	50	660	660	0	0	G1/2"	70	15.4	
	60	200	380	1	1	570-3C 60 620	60	60	620	620	0	0	G3/4"	70	15.6	
	60	380	560	1	1	570-3C 60 800	60	60	800	800	0	0	G3/4"	70	15.6	

Inch version

							Dimensions, inch									
CZC _{MS}	CZC _{WS}	OHN	OHX	CNSC	CXSC	Ordering code	DCON _{MS}	DCON _{WS}	LPR	LF	WF	HF	CNT	CP BarPSI	Lbs	
5/8	16	2.165	3.583	1	3	A570-3C D10 06-16	.625	.630	6.142	6.142	.000	.000	G1/8"	1015	0.5	
3/4	20	3.071	4.449	1	3	A570-3C D12 08-20	.750	.787	7.874	7.874	.000	.000	G1/8"	1015	0.9	
1	25	3.346	6.220	1	3	A570-3C D16 10-25	1.000	.984	10.197	10.197	.000	.000	G1/4"	1015	1.8	
	25	6.102	9.213	1	3	A570-3C D16 13-25	1.000	.984	13.213	13.189	.000	.000	G1/4"	1015	2.8	
	25	3.346	6.220	1	1	SL-3C D16 10-25	1.000	.984	10.200	10.200	.000	.000	G 1/4"	1015	4.6	
1 1/4	25	6.102	9.213	1	1	SL-3C D16 13-25	1.000	.984	13.213	13.213	.000	.000	G 1/4"	1015	6.3	
	32	3.937	7.480	1	1	A570-3C D20 12-32	1.250	1.260	12.480	12.480	.000	.000	G3/8"	1015	3.5	
1 1/2	32	7.559	11.260	1	1	A570-3C D20 16-32	1.250	1.260	16.221	16.221	.000	.000	G3/8"	1015	4.8	
	32	5.039	9.252	1	1	A570-3C D24 15-32	1.500	1.260	15.264	15.264	.120	.000	G1/2"	1015	6.8	
	32	9.764	13.740	1	1	A570-3C D24 20-32	1.500	1.260	19.803	19.803	.120	.000	G1/2"	1015	6.8	

EasyFix for 16-25 mm (.625-1.000 inch)



I1



I38