


実用小型引張バネ

フック内側自由長さ

製品番号	外 径	線 径	自由長さ	最大たわみ	最大荷重	初 張 力	ばね定数	1袋入数
	mm	mm	mm	mm	kgf	kgf	kgf/mm	個
E05-01	5.0	0.32	14.9	22.0	0.158	0.018	0.0064	20
E05-02		0.32	17.8	34.2	0.158	0.018	0.0041	
E05-03		0.32	22.6	53.9	0.158	0.018	0.0026	
E05-04		0.32	29.9	87.7	0.158	0.018	0.0016	
E05-05		0.4	15.8	15.9	0.309	0.052	0.0164	
E05-06		0.4	19.4	24.7	0.309	0.052	0.0105	
E05-07		0.4	25.4	39.1	0.309	0.052	0.0066	
E05-08		0.4	34.6	61.4	0.309	0.052	0.0042	
E05-09		0.5	17.1	11.3	0.611	0.134	0.0429	
E05-10		0.5	21.6	17.6	0.611	0.134	0.0274	
E05-11		0.5	29.1	28.1	0.611	0.134	0.0171	
E05-12		0.5	40.6	44.0	0.611	0.134	0.0109	
E05-13		0.6	18.3	8.7	1.069	0.270	0.0951	
E05-14		0.6	23.7	13.4	1.069	0.270	0.0609	
E05-15		0.6	32.7	21.3	1.069	0.270	0.0380	
E05-16		0.6	46.7	33.3	1.069	0.270	0.0241	
E063-01	6.3	0.4	18.7	27.4	0.241	0.029	0.0078	20
E063-02		0.4	22.3	42.6	0.241	0.029	0.0050	
E063-03		0.4	28.3	68.6	0.241	0.029	0.0031	
E063-04		0.4	37.5	106.2	0.241	0.029	0.0020	
E063-05		0.5	19.9	20.0	0.474	0.080	0.0200	
E063-06		0.5	24.4	31.1	0.474	0.080	0.0128	
E063-07		0.5	31.9	49.6	0.474	0.080	0.0080	
E063-08		0.5	43.4	77.6	0.474	0.080	0.0051	
E063-09		0.6	21.1	15.3	0.825	0.171	0.0437	
E063-10		0.6	26.5	23.7	0.825	0.171	0.0280	
E063-11		0.6	35.5	37.7	0.825	0.171	0.0175	
E063-12		0.6	49.3	59.2	0.825	0.171	0.0111	
E063-13		0.7	22.3	12.0	1.310	0.320	0.0854	
E063-14		0.7	28.6	18.5	1.310	0.320	0.0547	
E063-15		0.7	39.1	29.3	1.310	0.320	0.0342	
E063-16		0.7	55.2	46.0	1.310	0.320	0.0217	
E063-17		0.8	23.5	9.8	1.973	0.530	0.1539	
E063-18		0.8	30.7	15.0	1.973	0.530	0.0985	
E063-19		0.8	42.7	23.9	1.973	0.530	0.0615	
E063-20		0.8	61.1	37.3	1.973	0.530	0.0391	
E08-01	8.0	0.6	24.9	27.3	0.636	0.097	0.0200	10
E08-02		0.6	30.3	42.4	0.636	0.097	0.0128	