

Silent Smooth Castors I



—Medium duty type—

RoHS compliant products.

POINT

- **Low rolling noise** compared to our standard pressed castors (p.13).
 - Thanks to **combination of thrust bearing and ball bearing** in the swivel head, it **moves lightly and turns easily**.
 - Wheel with grease-packed precision ball bearings.
 - **Smooth and silent rolling** without subsequent lubrication.
- NB Please contact us if you use this series in combination with fixed castors.

USE EXAMPLE

- For various carriers.
- ©We'll accept your custom-order. Please feel free to contact us.
(Use "Specification Form for Custom-designed castor" at the end of this catalog.)
©Please feel free to ask about the product weight for each item.

JS Swivel castors



JS-100

JS-130

JS-150

JS-200

- Color/Finish; Zinc plated

7

Silent Smooth Castors I

ベアリング変更 (MCは除く) JBB→CB

WHEELS JBB ... Radial ball bearing

See P.62 to P.71 for detailed description.



→P.70

W (SBR)



→P.68

JBB SST (NR)

- Runs more lightly compared with W!
 - Impact resistance: 1.8 times higher than W. Starting performance: 2.5 times better than W.
- NB φ100, 150 and 200.



→P.70

JBB UW (UR)



→P.70

JBB WUW (Antibacterial UR/White)

- Antibacterial effect, oil resistance and high elasticity.
- Floor saving and non-marking.



→P.64

JBB MC (Monomer cast nylon)

JBB