

Circular Saw Guide L-Angle Plus



73152

- Features both shaku and metric graduations to come in handy for carpenters
- Aluminum construction makes guide both light and sturdy. Features white graduations on a blue background.



73150



73151



73153

●Parts are listed from p.243

Item Code	Description	Body Size (mm)	Weight (g)	JAN Code	Packing Unit	Package
73150	45 cm/shaku	632×350×83	1,100	4 960910 731509	2	B
73151	60 cm/shaku	762×350×83	1,200	4 960910 731516		
73152	1 m/shaku	1,162×400×83	1,600	4 960910 731523	1	N
73153	1.2 m/shaku	1,362×400×83	1,700	4 960910 731530		

Refer to P. 2 about the shaku scale

Features

- Wide Hex Grip that grips securely.



- Slides in easily and secures tightly with Slide-Stop System. It slides smoothly since the non-slip rubber is normally floating above the surface. Pressing down on the handle causes the rubber portion to move down and adhere to the material, securing it tightly.

Slides in easily



Fastens quickly




- Heel shape that stands completely straight. The product will not become diagonal when stood upright since the guide and the handle mounting board have the same height.



- Enables square cuts just by aligning base plate of electric circular saw along the edge of the guide
- Features both shaku and metric graduations to come in handy for carpenters

- Aluminum construction makes guide both light and sturdy. Features white graduations on a blue background.



- Non-slip rubber pad achieves high non-slip performance thanks to the use of the high-performance microcellular polymer sheet PORON®, which has a high-density, delicate and uniform cell structure



- With groove for slider (sold separately, item code 78236) - just slide it in the groove to prevent shifting during cutting
- Stainless steel plate on guide edge

Use

- As a guide rule when making square cuts on boards with an electric circular saw
- For dimension measurements

Specifications

Item Code	73150	73151	73152	73153
Perpendicularity	Less than 0.1 mm per 100 mm			
Graduation	1 shaku 6 sun 5 bu	2 shaku	3 shaku 3 sun	4 shaku
	50 cm	60 cm	1 m	1.2 m
Edge Height	15 mm			
Material	Body: Aluminum Guide Surface: Stainless steel Protective End Cap: ABS resin Wide Handle: ABS resin, elastomer resin			
Accessories	cutout positioning stick			