

Thermo/Hygrometer for Room Conditioning



70501



70506



70514

Item Code	Description	Body Size (mm)	Weight (g)	JAN Code	Packing Unit	Package
70501	F-2L 15 cm Blue	φ156×30	142	4 960910 705012	5	SP
70506	F-2M 10 cm Blue	φ106×30	70	4 960910 705067		
70514	F-2S 6.5 cm Blue	φ71×21	30	4 960910 705142		

Features

- Ideal for saving energy with displays of suggested temperature and comfortable humidity
- With hook hole



Use

- For temperature and humidity control at homes, in classrooms and offices, etc.

Specifications

Item Code	70501	70506	70514
Accuracy	<Temperature> -20 - 40°C: ±2°C Other values: ±4°C		<Temperature> -20 - 40°C: ±2°C
Measuring Range	Temperature: -24 - 44°C Humidity: 5 - 95%		Temp: -20 - 40°C Humidity: 10 - 90%
Each Graduation	Temperature: 2°C Humidity: 5%		
Material	Body: Polystyrene resin, ABS resin Scale Plate Cover: Polystyrene resin Scale Plate: Iron Pointer: Aluminum		

Thermo/Hygrometer for Heatstroke Warning



70505



70507



70515

Item Code	Description	Body Size (mm)	Weight (g)	JAN Code	Packing Unit	Package
70505	F-3L II 15 cm White	φ156×30	150	4 960910 705050	5	SP
70507	F-3M 10 cm White	φ106×30	73	4 960910 705074		
70515	F-3S 6.5 cm White	φ71×21	33	4 960910 705159		

Features

- Shows five levels of warning for heatstroke
- With hook hole



Use

- For temperature and humidity control at homes, in classrooms and offices, etc.

Specifications

Item Code	70505	70507	70515
Accuracy	<Temperature> -20 - 40°C: ±2°C <Humidity> 35 - 75%: ±5% Other values: ±10%		
Measuring Range	Temperature: -20 - 40°C Humidity: 10 - 90%		
Each Graduation	Temperature: 2°C Humidity: 5%		
Material	Body: Polystyrene resin, ABS resin Scale Plate Cover: Polystyrene resin Scale Plate: Iron Pointer: Aluminum		

Thermo/Hygrometer for Heatstroke Warning Rainproof



70600



Large openings on back for quick response to changes in temperature, humidity, and heat stroke levels.

Rainproof structure offers protection even during rain.



Item Code	Description	Body Size (mm)	Weight (g)	JAN Code	Packing Unit	Package
70600	F-3L II 15 cm Red	φ156×38	160	4 960910 706002	5	SP

Features

- Heatstroke warning indicator with rainproof function
- Shows five levels of warning for heatstroke
- With hook hole

Use

- For temperature and humidity control in building, construction, farming, the home, classroom, or office, etc.

Specifications

Accuracy	<Temperature> -20 - 40°C: ±2°C Other values: ±4°C <Humidity> 35 - 75%: ±5% Other values: ±10%
Measuring Range	Temperature: -20 - 50°C Humidity: 10 - 90%
Each Graduation	Temperature: 2°C Humidity: 5%
Waterproof*1	IPX3*2
Material	Body: Polystyrene resin, ABS resin Scale Plate Cover: AS resin Scale Plate: Iron Pointer: Aluminum Waterproof Cloth: Nylon, polyurethane resin

- *1 Waterproof performance protects internal functions, but device cannot measure accurately when wet.
- *2 Not adversely affected by rain falling within 60° from either left or right.