

Digital Thermo/Hygrometer, Thermometer Smart



Item Code	Description	Body Size (mm)	Weight (g)	JAN Code	Packing Unit	Package
73115	Digital Thermo/Hygrometer Smart A	103×102×18	135	4 960910 731158	5	
73116	Digital Thermometer Smart A	70×102×18	95	4 960910 731165		
73117	Digital Thermometer Smart B for Indoor and Outdoor with Waterproof Outside Sensor	70×102×18	115	4 960910 731172		
73118	Digital Thermometer Smart C Maximum and Minimum for Indoor and Outdoor with Waterproof Outside Sensor	103×102×18	150	4 960910 731189		

Features

- Bright, low-glare liquid crystal display with wide-viewing angle and clear font
- Flat surface model with stylish exterior. Ideal for temperature control in a space where appearance is important.
- External sensor is water-resistant for worry-free use even on a rainy day
- Folding stand for setting upright, and hook hole for hanging on wall



Use

- For temperature and humidity control at homes, in classrooms and offices, etc.

Specifications

Item Code	73115	73116	73117	73118
Accuracy	<Temp.> 0 - 40°C ±1°C Other values ±2°C <Humidity> 40 - 80% ±10% Other values ±15%	0 - 40°C: ±1°C Other values: ±2°C		
Measuring Range	Temperature: -5 - 49°C Humidity: 30 - 91%	-5 - 50°C	Internal sensor: -5 - 50°C External sensor: -49 - 70°C	Internal sensor: -5 - 50°C External sensor: -50 - 70°C
Minimum Display	Temperature: 0.1°C Humidity: 1%	0.1°C		
Measuring Interval	20 seconds	6 seconds	10 seconds	
Power Source	1x AAA alkaline battery (Battery included is for trial use only and may not last as long)			
Waterproof	-		External sensor: IPX7 *	
Material	Body: ABS resin		Body: ABS resin External Sensor: Stainless steel, vinyl chloride resin	
Size	-		External Sensor: φ4.5 × 13 mm Cord Length: 3 m	

*Water will not penetrate even if temporarily submerged (within 30 minutes) at a depth up to 1 m.

Digital Thermo/Hygrometer Home A



Features

- Bright, low-glare liquid crystal display with wide-viewing angle and clear font
- Display can switch between maximum temperature/humidity and minimum temperature/humidity
- Can be used in a wide range of locations thanks to its compact and simple design that suits any interior
- Can be propped up with its folding stand, or hung on a wall with its hook hole



On the table



On the wall



- Clear package recommended for gifts

Use

- For temperature and humidity control at homes, in classrooms and offices, etc.

Specifications

Accuracy	<Temp.> 0 - 40°C: ±1°C Other Values: ±2.5°C <Humidity> 40 - 80%: ±10% Other Values: ±15%
Measuring Range	Temp.: -5 - 49°C Humidity: 30 - 95%
Minimum Display	Temp.: 0.1°C Humidity: 1%
Measuring Interval	10 seconds
Material	Body: ABS resin
Power Source	1x AAA alkaline battery (Battery included is for trial use only and may not last as long)