



Scaling Hammers/ Needle Scalers

- Hardened pistons and cylinders for longer life
- Simple structure for easy maintenance



TS-2

- Compact and handy needle scalers
- Precision heat-treated needles for maximum performance



TNS-200



TNS-200PS

N-200

Scaling Hammers Specifications: Air pressure 6kg/cm²

MODEL	Piston Dia (mm)	Piston Stroke (mm)	Net Weight (kg)	Blow per Min (bpm)	Overall Length (mm)	Air Cons. Free (m ³ /min)	Air Inlet (PT)	Hose Size (in)
TS-2	30	30	2.2	8000	500	0.3	3/8	1/2

Needle Scalers Specifications: Air pressure 6kg/cm²

MODEL	Piston Dia (mm)	Blow per Min (bpm)	Needle Dia Length, Number (mm)×(mm)×Piece	Piston Stroke (mm)	Net Weight (kg)	Overall Length (mm)	Air Cons. Free (m ³ /min)	Air Inlet (PT)	Hose Size (in)
N-200	20	12000	3×125×12	12	1.12	225	0.25	1/4	1/4
TNS-200	20	4000	3×180×12	25	2.4	345	0.25	1/4	3/8
TNS-200PS	20	3500	3×180×12	25	1.6	305	0.25	1/4	3/8