

Prices displayed include 8% tax.

Mitutoyo Stock 466 Items

"ABS Digimatic Caliper" (Solar Type)

Repairing OK Calibration OK Approx. 2 Weeks



- Features** • Built-in ABS scale eliminates origin alignment for each power on. • The minimum required illuminance is 60lux, which is a solar battery loaded type that can be used regardless of location as long as there is average everyday brightness. • CE standard product.
- Use** • Step measurement, inner measurement, outer measurement, depth measurement, and the like.
- Specs** • Power supply: Solar battery
- Origin** • Japan
- SPQ: 1 Piece

Order Unit: 1 Piece

MITUTOYO CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Manufacturer Code	Measurement Range (mm)	Instrument Error (mm)	Minimum Display (mm)	Outer Side Jaws (mm)	Interior Jaws (mm)	Depth Bar	Weight (g)
262-9135	CD-S10C	¥17,213	¥17,000	500-443	0 to 100	±0.02	0.01	40	16.5	Yes (round 1.9)	145
105-2152	CD-S15C	¥17,718	¥17,500	500-444	0 to 150	±0.02	0.01	40	16.5	Yes	170
105-2161	CD-S20C	¥21,768	¥21,500	500-445	0 to 200	±0.02	0.01	50	20.0	Yes	200

Contact us: 050-3786-3214 <http://www.mitutoyo.co.jp/>

Mitutoyo Stock 466 Items

"ABS Digimatic Caliper" (constant pressure type)

Repairing OK Calibration OK Approx. 2 Weeks



- Features** • Accurate measurement can be performed for plastic products that are usually difficult to be measured with a normal caliper due to deformation. • Measuring force is 0.5 to 1.0N. • CE standard product.
- Use** • For outside measurement of soft material or object.
- Specs** • Power supply: Button type silver oxide battery (SR44) x 1 (accessory)
- Origin** • Japan
- SPQ: 1 Piece

Order Unit: 1 Piece

MITUTOYO CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Manufacturer Code	Measurement Range (mm)	Instrument Error (mm)	Minimum Display (mm)	Outer Side Jaws (mm)	Interior Jaws (mm)	Depth Bar	Weight (g)
763-2886	NTD25-20AX	¥56,903	¥56,200	573-191-30	0 to 180	±0.05	0.01	40	-	None	253

Contact us: 050-3786-3214 <http://www.mitutoyo.co.jp/>

Mitutoyo Stock 466 Items

"ABS Offset Digimatic Caliper"

Repairing OK Calibration OK



- Features** • Jaw of main scale can be slid up and down. • CE standard product.
- Use** • For measurement of uneven parts.
- Specs** • Container protection grade: IP67
- Origin** • Japan
- SPQ: 1 Piece

Order Unit: 1 Piece

MITUTOYO CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Manufacturer Code	Measurement Range (mm)	Instrument Error (mm)	Minimum Display (mm)	Outer Side Jaws (mm)	Interior Jaws (mm)	Depth Bar	SPQ (piece)	Weight (g)
833-8535	NTD10-P15M	¥32,198	¥31,800	573-601-20	0 to 150	±0.02	0.01	40	14	Yes	1	168
833-8536	NTD10-P20M	¥35,640	¥35,200	573-602-20	0 to 200	±0.02	0.01	50	14	Yes	1	198

Contact us: 050-3786-3214 <http://www.mitutoyo.co.jp/>

SK Stock 1,103 Items

Digital Caliper

Repairing OK Calibration OK Approx. 2 Weeks



- Features** • Easy to see with the digital display. • Has a hold function.
- Use** • With an inspection table.
- Specs** • For outer measurement, inner measurement, depth measurement, step difference measurement.
- Origin** • China
- SPQ: 1 Piece

Order Unit: 1 Piece

(Price revision date: Jun, 2015) NIIGATASEIKI Co.Ltd.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Manufacturer Code	Measurement Range (mm)	Instrument Error (mm)	Minimum Display (mm)	Outer Side Jaws (mm)	Interior Jaws (mm)	Depth Bar	Weight (g)
331-1163	DT-100	¥ 8,883	¥ 9,400	151291	0 to 100	±0.03	0.01	40	16.5	Yes	145
331-1171	DT-150	¥ 9,828	¥10,400	151292	0 to 150	±0.03	0.01	40	16.5	Yes	160
331-1180	DT-200	¥14,175	¥15,000	151293	0 to 200	±0.03	0.01	50	19.5	Yes	200
331-1198	DT-300	¥23,247	¥24,600	151294	0 to 300	±0.04	0.01	60	21.5	Yes	270

Contact us: 0256-31-5660 <http://www.sokuteikougou.com/>

SK Stock 1,103 Items

"Digital S-line Caliper"

Repairing OK Calibration OK Approx. 2 Weeks RoHS



- Features** • Protection grade is IP67.
- Use** • For outside measurement, inside measurement, depth measurement, and step difference measurement.
- Specs** • Protection grade IP67
- Origin** • Switzerland
- SPQ: 1 Piece

Order Unit: 1 Piece

(Price revision date: Nov, 2016) NIIGATASEIKI Co.Ltd.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Manufacturer Code	Measurement Range (mm)	Instrument Error (mm)	Minimum Display (mm)	Outer Side Jaws (mm)	Interior Jaws (mm)	Depth Bar	Weight (g)
418-7202	D-150IP67S	¥19,440	¥18,000	152006	0 to 150	±0.02	0.01	40	16	Yes	170
418-7229	D-200IP67S	¥30,780	¥28,500	152007	0 to 200	±0.03	0.01	50	19	Yes	200
418-7237	D-300IP67S	¥42,012	¥38,900	152008	0 to 300	±0.03	0.01	64	19	None	270

Contact us: 0256-31-5660 <http://www.sokuteikougou.com/>

Warning
• For instrument error, 0.02mm is added except for outside measurement.