

Prices displayed include 8% tax.

TRUSCO Stock 38,650 Items

Grip Knob



TGKB Type (external thread type)



TGKN Type (internal thread type)



Features •Dimple in the outer circumference enhances operability.

Specs •Heat Resistant Temperature: 70° C

Materials •Knob: ABS Resin Origin •Japan

External Thread Type Materials •External Thread: Steel (trivalent chromate)

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Outer Diameter (mm)	Knob Height (mm)	Screw Dimension	Screw Length (mm)	SPQ (piece)	Weight (g)
430-9316	TGKB1-M3X10	¥166	¥180	16	12	M3 x 0.50	10	150	2.8
430-9324	TGKB1-M3X15	¥166	¥180	16	12	M3 x 0.50	15	150	3.0
430-9332	TGKB1-M4X10	¥166	¥180	16	12	M4 x 0.70	10	120	3.4
430-9341	TGKB1-M4X15	¥166	¥180	16	12	M4 x 0.70	15	120	3.8
430-9359	TGKB1-M5X10	¥166	¥180	16	12	M5 x 0.80	10	100	4.5
430-9367	TGKB1-M5X15	¥166	¥180	16	12	M5 x 0.80	15	100	5.1
430-9375	TGKB1-M5X20	¥166	¥180	16	12	M5 x 0.80	20	100	5.6
430-9383	TGKB2-M5X15	¥166	¥180	20	14	M5 x 0.80	15	100	6.6
430-9391	TGKB2-M5X20	¥166	¥180	20	14	M5 x 0.80	20	100	7.2
430-9405	TGKB2-M6X10	¥166	¥180	20	14	M6 x 1.00	10	100	7.2
430-9413	TGKB2-M6X15	¥166	¥180	20	14	M6 x 1.00	15	100	8.0
430-9421	TGKB2-M6X20	¥166	¥180	20	14	M6 x 1.00	20	100	8.9
430-9430	TGKB3-M5X20	¥204	¥220	25	18	M5 x 0.80	20	50	10.8
430-9448	TGKB3-M5X25	¥204	¥220	25	18	M5 x 0.80	25	50	11.4
430-9456	TGKB3-M6X15	¥204	¥220	25	18	M6 x 1.00	15	50	11.8
430-9464	TGKB3-M6X20	¥204	¥220	25	18	M6 x 1.00	20	50	12.6
430-9472	TGKB3-M6X25	¥204	¥220	25	18	M6 x 1.00	25	50	13.5
430-9481	TGKB4-M8X15	¥249	¥270	32	18	M8 x 1.25	15	50	20.2
430-9499	TGKB4-M8X20	¥249	¥270	32	18	M8 x 1.25	20	50	22.2
430-9502	TGKB4-M8X25	¥249	¥270	32	18	M8 x 1.25	25	50	23.7

Internal Thread Type Materials •Internal Thread: Brass (RoHS compliant material cadmium 75ppm or less)

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Outer Diameter (mm)	Knob Height (mm)	Screw Dimension	Screw Height (mm)	SPQ (piece)	Weight (g)
430-9715	TGKN2-M5	¥185	¥200	20	14	M5 x 0.80	6	150	5.2
430-9723	TGKN2-M6	¥185	¥200	20	14	M6 x 1.00	6	150	5.6
430-9731	TGKN4-M8	¥314	¥340	32	18	M8 x 1.25	9	60	15.2

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock 38,650 Items

Grip Knob Long



TGKBL Type (external thread type)



TGKNL Type (internal thread type)



Features •Dimples in the outer circumference enhance operability.

•Long type easy to grab.

Specs •Heat Resistant Temperature: 70° C

Materials •Knob: ABS Resin Origin •Japan

External Thread Type Materials •External Thread: Steel (trivalent chromate)

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Outer Diameter (mm)	Knob Height (mm)	Screw Dimension	Screw Length (mm)	SPQ (piece)	Weight (g)
430-9511	TGKBL1-M3X10	¥194	¥210	16	16	M3 x 0.50	10	100	3.2
430-9529	TGKBL1-M3X15	¥194	¥210	16	16	M3 x 0.50	15	100	3.4
430-9537	TGKBL1-M4X10	¥194	¥210	16	16	M4 x 0.70	10	100	3.9
430-9545	TGKBL1-M4X15	¥194	¥210	16	16	M4 x 0.70	15	100	4.2
430-9553	TGKBL1-M5X10	¥194	¥210	16	16	M5 x 0.80	10	100	5.1
430-9561	TGKBL1-M5X15	¥194	¥210	16	16	M5 x 0.80	15	100	5.7
430-9570	TGKBL1-M5X20	¥194	¥210	16	16	M5 x 0.80	20	100	6.3
430-9588	TGKBL2-M5X15	¥241	¥260	20	22	M5 x 0.80	15	80	9.5
430-9596	TGKBL2-M5X20	¥241	¥260	20	22	M5 x 0.80	20	80	10.1
430-9600	TGKBL2-M6X10	¥249	¥270	20	22	M6 x 1.00	10	80	10.4
430-9618	TGKBL2-M6X15	¥249	¥270	20	22	M6 x 1.00	15	80	11.1
430-9626	TGKBL2-M6X20	¥249	¥270	20	22	M6 x 1.00	20	80	12.2
430-9634	TGKBL3-M5X20	¥241	¥260	25	27	M5 x 0.80	20	40	14.6
430-9642	TGKBL3-M5X25	¥241	¥260	25	27	M5 x 0.80	25	40	15.1
430-9651	TGKBL3-M6X15	¥249	¥270	25	27	M6 x 1.00	15	40	15.7
430-9669	TGKBL3-M6X20	¥249	¥270	25	27	M6 x 1.00	20	40	16.7
430-9677	TGKBL3-M6X25	¥249	¥270	25	27	M6 x 1.00	25	40	17.5
430-9685	TGKBL4-M8X15	¥334	¥360	32	27	M8 x 1.25	15	40	28.0
430-9693	TGKBL4-M8X20	¥334	¥360	32	27	M8 x 1.25	20	40	29.5
430-9707	TGKBL4-M8X25	¥334	¥360	32	27	M8 x 1.25	25	40	40.0

Internal Thread Type Materials •Internal Thread: Brass (RoHS compliant material cadmium 75ppm or less)

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Outer Diameter (mm)	Knob Height (mm)	Screw Dimension	Screw Height (mm)	SPQ (piece)	Weight (g)
430-9740	TGKNL2-M5	¥249	¥270	20	22	M5 x 0.80	15	100	7.5
430-9758	TGKNL2-M6	¥278	¥300	20	22	M6 x 1.00	15	100	7.9
430-9766	TGKNL4-M8	¥435	¥470	32	27	M8 x 1.25	16	40	21.1

Contact us:0120-509-849 <http://www.orange-book.com/>