

HAMMER CASTER

Stock
793
Items

Threaded Type Caster (rubber wheel/stainless steel metal fittings)




Features •All-stainless steel is excellent in corrosion resistance and water resistance.
Specs •Threaded type
Materials •Metal Fitting: Stainless Steel (SUS304) •Wheel: Rubber Origin •Japan



320EA-R65-BAR01

Dimensions



Flexible Specs •Flexible Type

Order Unit: 1 Piece

HAMMER CASTER Co.Ltd.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Allowable Weight (daN) (kgf)		Wheel Diameter D (mm)	Wheel Width (mm)	Mounting Height H (mm)	Shaft Length L (mm)	Screw T	Thread Pitch (mm)	SPQ (piece)	Weight (g)
398-4427	320EA-R50-BAR01	¥ 986	-	30	30.6	50	20	68	35	M12	1.75	4	181
398-4435	320EA-R65-BAR01	¥1,180	-	30	30.6	65	21	85	35	M12	1.75	4	231
398-4443	320EA-R75-BAR01	¥1,271	-	40	40.8	75	21	95	35	M12	1.75	4	274
398-4419	320EA-R100-BAR01	¥2,384	-	50	51.0	100	27	126	40	M16	2.00	2	621

Plate Type Rubber Casters

Plate Type Urethane Casters

Plate Type Nylon Casters

Plate Type Resin Casters

Screwed Rubber Casters

Screwed Urethane Casters

Screwed Nylon Casters

Screwed Resin Casters

Nuts, Spanners

Stem Casters

Stainless Steel Casters

Angle Casters

Corner Casters

Dual Wheel Casters

Sound Reducing Casters

ESD-Safe Casters

Shock Absorbing Casters

Casters for Specific Environment

Pneumatic/No-Puncture Caster

Low Level Casters

Heavy-Duty Casters


Casting Casters

Stoppers



315EA-R75-BAR01

Dimensions



Flexible with stopper Specs •Flexible Type (with stopper)

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Allowable Weight (daN) (kgf)		Wheel Diameter D (mm)	Wheel Width (mm)	Mounting Height H (mm)	Shaft Length L (mm)	Screw T	Thread Pitch (mm)	SPQ (piece)	Weight (g)
398-4265	315EA-R50-BAR01	¥1,219	-	30	30.6	50	20	68	35	M12	1.75	4	211
398-4273	315EA-R65-BAR01	¥1,317	-	30	30.6	65	21	85	35	M12	1.75	4	261
398-4281	315EA-R75-BAR01	¥1,425	-	40	40.8	75	21	95	35	M12	1.75	4	305
398-4257	315EA-R100-BAR01	¥2,578	-	50	51.0	100	27	126	40	M16	2.00	2	679

URL <http://www.hammer-caster.co.jp/>

TRUSCO

Stock
38,650
Items

Threaded type Conductive Caster (rubber wheel/stainless steel fittings)

Features •Since it is made of stainless steel, it has excellent corrosion resistance and water resistance.
•Discharge of static electric is easy due to usage of electro conductive rubber wheel, also excellent in dust absorption prevention effect.

Specs •Threaded type •Surface Resistivity: $10^4 \Omega$ (measured value, not guaranteed value)

Materials •Metal Fitting: Stainless Steel (SUS304)

•Wheel: Conductive Rubber

Origin •Japan

Flexible Specs •Flexible Type

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Allowable Weight (daN) (kgf)		Wheel Diameter D (mm)	Wheel Width (mm)	Mounting Height H (mm)	Shaft Length L (mm)	Screw T	Thread Pitch (mm)	SPQ (piece)	Weight (g)
278-3061	TYSSST-100RHE	¥2,296	¥2,480	50	51	100	25	126	35	M12	1.75	20	480

.Com Drawing



TYSSST-100RHE

Dimensions



Flexible with stopper Specs •Flexible Type (with stopper)

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Allowable Weight (daN) (kgf)		Wheel Diameter D (mm)	Wheel Width (mm)	Mounting Height H (mm)	Shaft Length L (mm)	Screw T	Thread Pitch (mm)	SPQ (piece)	Weight (g)
278-3070	TYSSST-100RHES	¥2,582	¥2,790	50	51	100	25	126	35	M12	1.75	20	530

Contact us:0120-509-849 <http://www.orange-book.com/>

YUEI

Stock
700
Items

Threaded Type Caster "3/4 Size" (urethane wheel/stainless steel fittings)

Features •Fully made of stainless steel fittings with excellent water resistance and corrosion resistance.

•Widely used for food processing machinery and kitchen equipment.

Specs •Threaded type

Materials •Metal Fitting: Stainless Steel (SUS304)

•Wheel: Nylon Wheel, Urethane

Origin •Japan

Flexible Specs •Flexible Type

Order Unit: 1 Piece

YUEI CASTER Co.Ltd

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Allowable Weight (daN) (kgf)		Wheel Diameter D (mm)	Wheel Width (mm)	Mounting Height H (mm)	Shaft Length L (mm)	Screw T	Number of Ridges	SPQ (piece)	Weight (g)
440-5846	SUS-ST-75UR-W3/4-40	¥3,128	-	70	71.4	75	26	97	40	W3/4	10 Ridges	40	335
440-5471	SUS-ET-100UR-W3/4-40	¥3,336	-	60	61.2	100	28	126	40	W3/4	10 Ridges	24	410

Flexible with stopper Specs •Flexible Type (with stopper)

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Allowable Weight (daN) (kgf)		Wheel Diameter D (mm)	Wheel Width (mm)	Mounting Height H (mm)	Shaft Length L (mm)	Screw T	Number of Ridges	SPQ (piece)	Weight (g)
440-5838	SUS-ST-75URS-W3/4-40	¥3,396	-	70	71.4	75	26	97	40	W3/4	10 Ridges	35	390
440-5463	SUS-ET-100URS-W3/4-40	¥3,560	-	60	61.2	100	28	126	40	W3/4	10 Ridges	20	475


Contact us:06-6747-5618 <http://www.yueicaster.co.jp/>

.Com CAD



SUS-ST-75UR-W3/4-40

Dimensions



SUS-ST-75URS-W3/4-40

Dimensions

