

The number next to the logo mark indicates items in stock for each brand.

Plate Type Rubber Casters

Plate Type Urethane Casters

Plate Type Nylon Casters

Plate Type Resin Casters

Screwed Rubber Casters

Screwed Urethane Casters

Screwed Nylon Casters

Screwed Resin Casters

Nuts, Spanners

Stem Casters

Stainless Steel Casters

Angle Casters

Corner Casters

Dual Wheel Casters

Sound Reducing Casters

ESD-Safe Casters

Shock Absorbing Casters

Casters for Specific Environment

Pneumatic/No-Puncture Caster

Low Level Casters

Heavy-Duty Casters

Casting Casters

Stoppers

TRUSCO **Stock 38,650 Items**

## Lock Stopper (made of steel)



- Features**
- Excellent operability/durability, safe steel-made floor lock.
  - Locks by pushing against the floor surface due to function of built-in spring. (the dolly cannot be lifted when locked.)
- Materials** •Steel
- Origin** •Japan



TLS909-WJ1-BAR01

**Warning**

- Please follow the proper mounting height. The mounting height of rubber wheel decreases depending on the load.

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Appropriate Mounting Height (mm)	Min Height (mm)	Max Height (mm)	Stroke (mm)	Mounting Plate (mm)	Mounting Pitch (mm)	SPQ (piece)	Weight (kg)
485-6848	TLS909-WJ1-BAR01	¥3,518	¥3,800	144	124	149	25	120 x 120	85 to 100 x 85 to 100	10	1.1
485-6856	TLS909-WJ2-BAR01	¥3,703	¥4,000	198	178	203	25	120 x 120	85 to 100 x 85 to 100	10	1.2
485-6864	TLS909-WJ3-BAR01	¥3,888	¥4,200	250	230	255	25	120 x 120	85 to 100 x 85 to 100	10	1.3

TRUSCO NAKAYAMA CORPORATION

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**

## Lock Stopper Set for Steel Made Transportation Cart (made of steel)

- Features**
- Excellent operability/durability, safe steel-made floor lock.
  - Locks by pushing against the floor surface due to function of built-in spring. (the dolly cannot be lifted when locked.)
- Materials** •Steel
- Origin** •Japan



(lock stopper)



(spacer for installation) (bolt and washer set)

LSH-1SET

Order Unit: 1 Set

Order Code	Item No.	Price (per set)	MSRP (per set)	Set Contents	SPQ (set)	Weight (kg/set)
783-5051	LSH-1SET	¥4,647	¥5,020	TLS909-WJ3-BAR01 + TLS-909-02A-100 x 2 + Bolt Set	1	1.9
783-5060	LSH-2SET	¥4,212	¥4,550	TLS909-WJ2-BAR01+TLS-909-02A-100 x 1 + Bolt Set	1	1.6
783-5078	LSH-3SET	¥3,777	¥4,080	TLS909-WJ1-BAR01 + Bolt Set	1	1.2
783-5086	LSP-1SET	¥4,814	¥5,200	TLS909-WJ2-BAR01+TLS-909-02A-100 3 pieces+Bolt set	1	2.2
783-5094	LSP-2SET	¥4,814	¥5,200	TLS909-WJ2-BAR01+TLS-909-02A-100 3 pieces+Bolt set	1	2.2
783-5108	LSP-3SET	¥4,351	¥4,700	TLS909-WJ1-BAR01+TLS-909-02A-100 2 pieces+Bolt set	1	1.8

TRUSCO NAKAYAMA CORPORATION

### Spacer for installation Materials •Steel

Order Unit: 1 Sheet

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	SPQ (sheet)	Weight (g)
773-3933	TLS-909-02A-100	¥249	¥270	1	278

TRUSCO NAKAYAMA CORPORATION

### Bolt/washer set

Order Unit: 1 Set

Order Code	Item No.	Price (per set)	MSRP (per set)	Compatible dollies	SPQ (set)	Weight (g/set)
782-9183	LSH-BTWS8X25	¥259	¥280	For SH-1N, SH-2N, SH-3N type	10	86
782-9191	LSP-BTWS10X25	¥334	¥360	For OH-3	10	140
782-9205	LSP-BTWS10X30	¥361	¥390	For OH-1 and OH-2 type	10	150

TRUSCO NAKAYAMA CORPORATION

Contact us:0120-509-849 <http://www.orange-book.com/>

SAMSUNG **Stock 167 Items**

## Stopper to Prevent Dolly from Moving (made of steel)

- Features**
- Fixing and Releasing are easy with one-touch action.
  - With balancing and leveling adjusting function of the surface Uneven.
  - As compressed springs are mounted within the pipes, demonstrate high braking force.
- Materials** •Metal Fitting: Steel
- Metal fitting surface treatment: powder coating and zinc plating
- Origin** •Korea



TPYFL-1



After leveling adjustment

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Allowable Weight (daN) (kgf)	Appropriate Mounting Height (mm)	Min Height (mm)	Max Height (mm)	Stroke (mm)	Mounting Plate (mm)	Mounting Pitch (mm)	SPQ (piece)	Weight (kg)
763-0395	TPYFL-1	¥7,020	¥8,670	294 300	190	178	202	24	120 x 120	83.5 x 83.5	2	2.40
763-0409	TPYFL-2	¥7,020	¥8,670	294 300	192	158	202	44	120 x 120	83.5 x 83.5	2	2.80

SAMSUNG CASTER CO. LTD.