

Prices displayed include 8% tax.

TRUSCO Stock 38,650 Items

Ball Chain



TBCS type



TBCB type

Example



Features •The chain itself has a fixing kink function, it can not twist.
Use •Hanging a plate, etc.
Origin •Japan

Example



Ball chain (brass) Materials •Brass (C2720) •Surface treatment: Chrome
Origin •England

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Total Length (m)	Ball Diameter (mm)	Working Load (kN)	SPQ (piece)	Weight (g)
828-7465	TBCB-2301A	¥ 296	¥ 320	1	2.3	0.02	5	11
828-7466	TBCB-2302A	¥ 528	¥ 570	2	2.3	0.02	5	22
828-7467	TBCB-2303A	¥ 778	¥ 840	3	2.3	0.02	5	33
828-7468	TBCB-2305A	¥1,250	¥1,350	5	2.3	0.02	5	55
828-7469	TBCB-2310A	¥2,462	¥2,660	10	2.3	0.02	5	110
828-7470	TBCB-2315A	¥3,694	¥3,990	15	2.3	0.02	5	165
828-7471	TBCB-3001A	¥ 352	¥ 380	1	3.0	0.04	5	16
828-7472	TBCB-3002A	¥ 620	¥ 670	2	3.0	0.04	5	32
828-7473	TBCB-3003A	¥ 926	¥1,000	3	3.0	0.04	5	48
828-7474	TBCB-3005A	¥1,490	¥1,610	5	3.0	0.04	5	80
828-7475	TBCB-3010A	¥2,953	¥3,190	10	3.0	0.04	5	160
828-7476	TBCB-3015A	¥4,425	¥4,780	15	3.0	0.04	5	240
828-7477	TBCB-4001A	¥ 482	¥ 520	1	4.0	0.05	5	27
828-7478	TBCB-4002A	¥ 879	¥ 950	2	4.0	0.05	5	54
828-7479	TBCB-4003A	¥1,398	¥1,510	3	4.0	0.05	5	81
828-7480	TBCB-4005A	¥2,129	¥2,300	5	4.0	0.05	5	135
828-7481	TBCB-4010A	¥4,194	¥4,530	10	4.0	0.05	5	270
828-7482	TBCB-4015A	¥6,286	¥6,790	15	4.0	0.05	5	405
828-7483	TBCB-4901A	¥ 648	¥ 700	1	4.9	0.16	5	45
828-7484	TBCB-4902A	¥1,203	¥1,300	2	4.9	0.16	5	90
828-7485	TBCB-4903A	¥1,796	¥1,940	3	4.9	0.16	5	135
828-7486	TBCB-4905A	¥2,944	¥3,180	5	4.9	0.16	5	225
828-7487	TBCB-4910A	¥5,847	¥6,317	10	4.9	0.16	5	450
828-7645	TBCB-4915A	¥8,773	¥9,477	15	4.9	0.16	5	675

Ball chain (stainless steel) Materials •Stainless Steel (SUS305)

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Total Length (m)	Ball Diameter (mm)	Working Load (kN)	SPQ (piece)	Weight (g)
498-2690	TBCS-2301	¥ 444	¥ 480	1	2.3	0.03	5	10
498-2703	TBCS-2302	¥ 833	¥ 900	2	2.3	0.03	5	20
498-2711	TBCS-2303	¥1,241	¥1,340	3	2.3	0.03	5	30
498-2720	TBCS-2305	¥2,027	¥2,190	5	2.3	0.03	5	50
498-2738	TBCS-2310	¥3,990	¥4,310	10	2.3	0.03	5	100
498-2746	TBCS-2315	¥5,990	¥6,470	15	2.3	0.03	5	150
498-2754	TBCS-3201	¥ 472	¥ 510	1	3.2	0.05	5	16
498-2762	TBCS-3202	¥ 879	¥ 950	2	3.2	0.05	5	32
498-2771	TBCS-3203	¥1,306	¥1,410	3	3.2	0.05	5	48
498-2789	TBCS-3205	¥2,138	¥2,310	5	3.2	0.05	5	80
498-2797	TBCS-3210	¥4,249	¥4,590	10	3.2	0.05	5	160
498-2801	TBCS-3215	¥6,369	¥6,880	15	3.2	0.05	5	240
498-2819	TBCS-4501	¥ 648	¥ 700	1	4.5	0.14	5	36
498-2827	TBCS-4502	¥1,203	¥1,300	2	4.5	0.14	5	72
498-2835	TBCS-4503	¥1,796	¥1,940	3	4.5	0.14	5	108
498-2843	TBCS-4505	¥2,953	¥3,190	5	4.5	0.14	5	180
498-2851	TBCS-4510	¥5,850	¥6,320	10	4.5	0.14	5	360
498-2860	TBCS-4515	¥8,702	¥9,400	15	4.5	0.14	5	540



TCNS type (ball chain connector)



TCNB type (ball chain connector)

Ball chain connector (stainless steel) Features •Connecting metal fitting of the ball chain. Easy to install.
Materials •Stainless Steel (SUS304)

Order Unit: 1 Bag

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Compatible Ball Diameter (mm)	Compatible Chain	Q'ty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
498-2916	TCNS-23	¥278	¥300	2.3	TBCS-2301 to 2315	10	5	0.9
498-2924	TCNS-32	¥314	¥340	3.2	TBCS-3201 to 3215	10	5	2.7
498-2932	TCNS-45	¥352	¥380	4.5	TBCS-4501 to 4515	10	5	7.6

Connection Example



TCPS type (ball chain coupling)



TCPB type (ball chain coupling)

Ball chain connector (brass) Features •Connecting metal fitting of the ball chain. Easy to install.
Materials •Brass (C2680R)

Order Unit: 1 Bag

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Compatible Ball Diameter (mm)	Compatible Chain	Q'ty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
498-2878	TCNB-23	¥158	¥170	2.3	TBCB-2301A to 2315A	10	5	1.7
498-2886	TCNB-30	¥176	¥190	3.0	TBCB-3001A to 3015A	10	5	3.1
498-2894	TCNB-40	¥204	¥220	4.0	TBCB-4001A to 4015A	10	5	4.9
498-2908	TCNB-50	¥231	¥250	4.9	TBCB-5001A to 5015A	10	5	8.5

Ball chain coupling (stainless steel) Features •Tip metal fitting of the ball chain. Easy to install.
Materials •Stainless Steel (SUS304)

Order Unit: 1 Bag

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Compatible Ball Diameter (mm)	Compatible Chain	Q'ty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
498-2983	TCPS-23	¥231	¥250	2.3	TBCS-2301 to 2315	10	5	0.7
498-2991	TCPS-32	¥278	¥300	3.2	TBCS-3201 to 3215	10	5	2.5
498-3009	TCPS-45	¥324	¥350	4.5	TBCS-4501 to 4515	10	5	8.1

Ball chain coupling (brass) Features •Tip metal fitting of the ball chain. Easy to install.
Materials •Brass (C2680R)

Order Unit: 1 Bag

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Compatible Ball Diameter (mm)	Compatible Chain	Q'ty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
498-2941	TCPB-23	¥158	¥170	2.3	TBCB-2301A to 2315A	10	5	0.9
498-2959	TCPB-30	¥176	¥190	3.0	TBCB-3001A to 3015A	10	5	3.8
498-2967	TCPB-40	¥204	¥220	4.0	TBCB-4001A to 4015A	10	5	5.9
498-2975	TCPB-50	¥231	¥250	4.9	TBCB-5001A to 5015A	10	5	9.6

Connection Example



Contact us:0120-509-849 <http://www.orange-book.com/>