

The number next to the logo mark indicates items in stock for each brand.



Stock 38,650 Items

Steel Wire

- Features •Iron wire plating is applied.
 Use •For uniting.
 Materials •Steel (SWMGS-2) •Surface treatment: Hot dip galvanizing
 Origin •China



TYW-26

Order Unit: 1 Roll (Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per roll)	MSRP (per roll)	Count	Wire Diameter (mm)	Length (m)	Working Load (kgf)	SPQ (roll)	Weight (kg)
282-5074	TYW-07	¥1,657	¥1,790	22	0.7	320	4	10	1
282-5066	TYW-09	¥1,490	¥1,610	20	0.9	200	7	10	1
282-5058	TYW-12	¥1,444	¥1,560	18	1.2	110	13	10	1
282-5040	TYW-16	¥1,342	¥1,450	16	1.6	60	21	10	1
282-5031	TYW-20	¥1,314	¥1,420	14	2.0	40	36	10	1
282-5023	TYW-26	¥1,194	¥1,290	12	2.6	23	60	10	1
282-5015	TYW-32	¥1,157	¥1,250	10	3.2	15	90	10	1
282-5007	TYW-40	¥1,157	¥1,250	8	4.0	10	140	10	1

Contact us:0120-509-849 <http://www.orange-book.com/>



Stock 38,650 Items

Steel Wire (small roll type)

- Features •Small roll type.
 Use •For gardening, farm, other works. •For uniting.
 Materials •Steel (SWMGS-2) •Surface treatment: Hot dip galvanizing
 Origin •China



TYWS-055

Order Unit: 1 Roll (Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per roll)	MSRP (per roll)	Count	Wire Diameter (mm)	Length (m)	Working Load (kgf)	SPQ (roll)	Weight (g)
359-9736	TYWS-03	¥241	¥260	30	0.30	20	0.36	10	11
759-3023	TYWS-035	¥259	¥280	28	0.35	17	0.40	10	26
759-3031	TYWS-045	¥259	¥280	26	0.45	15	0.80	10	23
359-9744	TYWS-055	¥241	¥260	24	0.55	12	3.00	10	22
359-9698	TYWS-07	¥565	¥610	22	0.70	70	4.00	20	212
359-9701	TYWS-09	¥537	¥580	20	0.90	40	7.00	20	200
359-9710	TYWS-12	¥482	¥520	18	1.20	25	13.00	20	222
359-9728	TYWS-16	¥482	¥520	16	1.60	15	21.00	20	237
759-3040	TYWS-20	¥768	¥830	14	2.00	10	36.00	20	247
759-3058	TYWS-26	¥768	¥830	12	2.60	6	60.00	20	250

Contact us:0120-509-849 <http://www.orange-book.com/>



Stock 38,650 Items

Stainless Steel Wire

- Features •Strong against rust and can be used for a long time.
 Use •It is used for gardening, farmlands and other bonds.
 •Uniting prone to rusting areas.

- Materials •Stainless Steel (SUS304)
 Origin •China



TSW-26

Order Unit: 1 Roll (Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per roll)	MSRP (per roll)	Count	Wire Diameter (mm)	Length (m)	Working Load (kgf)	SPQ (roll)	Weight (kg)
282-5635	TSW-09	¥4,425	¥4,780	20	0.9	200	14	10	1
282-5627	TSW-12	¥4,425	¥4,780	18	1.2	110	25	10	1
282-5619	TSW-16	¥4,370	¥4,720	16	1.6	62	43	10	1
282-5601	TSW-20	¥4,258	¥4,600	14	2.0	40	66	10	1
282-5597	TSW-26	¥4,258	¥4,600	12	2.6	23	83	10	1

Contact us:0120-509-849 <http://www.orange-book.com/>



Stock 38,650 Items

Stainless Steel Wire (small roll type)

- Features •Small roll type.
 Use •For gardening, farmlands and other bonds. •Uniting prone to rusting areas.
 Materials •Stainless Steel (SUS304) Origin •China



TSWS-16

Order Unit: 1 Roll (Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per roll)	MSRP (per roll)	Count	Wire Diameter (mm)	Length (m)	Working Load (kgf)	SPQ (roll)	Weight (g)
359-9671	TSWS-03	¥342	¥370	30	0.30	15	0.5	10	8
759-2990	TSWS-035	¥370	¥400	28	0.35	12	1.0	10	19
759-3007	TSWS-045	¥370	¥400	26	0.45	10	2.0	10	15
359-9680	TSWS-055	¥342	¥370	24	0.55	7	5.0	10	13
759-3015	TSWS-07	¥370	¥400	22	0.70	6	8.0	10	18
359-9639	TSWS-09	¥1,657	¥1,790	20	0.90	50	14.0	20	250
359-9647	TSWS-12	¥1,657	¥1,790	18	1.20	30	25.0	20	267
359-9655	TSWS-16	¥1,657	¥1,790	16	1.60	15	43.0	20	237
359-9663	TSWS-20	¥1,657	¥1,790	14	2.00	10	66.0	20	247

Contact us:0120-509-849 <http://www.orange-book.com/>