

FRL Unit/Filter Regulator

The number next to the logo mark indicates items in stock for each brand.



Stock 38,650 Items

FRL unit



Features • A unit that compactly connects an air filter, regulator and lubricator with an exclusive attachment.
Specs • Working fluid: Air • Fluid temperature: 5 to 60°C
 • Drain discharge method: Manual (however, automatically discharged when the pressure becomes 0.05MPa or less) • Working oil: Type 1 turbine oil (ISO VG#32 equivalent) • Pressure gauge with bracket
Origin • Taiwan

SPQ: 1 Piece

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Filtration Precision (μm)	Working Pressure (MPa)	Processing Air Volume (m ³ /min)	Set Pressure (MPa)	Oil Reservoir Capacity (cm ³)	Connection Port Diameter	Total Length x Total Width (mm)	Weight (kg)
496-0157	TACT403-8	¥11,583	¥14,300	5	0.05 to 1.0	0.8	0.1 to 0.85	200	Rc1/4	215 x 230	1.4
496-0131	TACT403-10	¥11,583	¥14,300	5	0.05 to 1.0	1.0	0.1 to 0.85	200	Rc3/8	215 x 230	1.4
496-0149	TACT403-15	¥11,583	¥14,300	5	0.05 to 1.0	1.5	0.1 to 0.85	200	Rc1/2	215 x 230	1.4

Contact us: 0120-509-849 <http://www.orange-book.com/>



TACT403-10



Stock 38,650 Items

FRL unit



Features • A unit that compactly connects a filter attached regulator and lubricator with an exclusive attachment.
Specs • Working fluid: Air • Fluid temperature: 5 to 60°C
 • Drain discharge method: Manual (however, automatically discharged when the pressure becomes 0.05MPa or less) • Working oil: Type 1 turbine oil (ISO VG#32 equivalent) • Pressure gauge with bracket
Origin • Taiwan

SPQ: 1 Piece

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Filtration Precision (μm)	Working Pressure (MPa)	Processing Air Volume (m ³ /min)	Set Pressure (MPa)	Oil Reservoir Capacity (cm ³)	Connection Port Diameter	Total Length x Total Width (mm)	Weight (kg)
496-0122	TACP403-8	¥10,854	¥13,400	5	0.05 to 1.0	0.8	0.1 to 0.85	200	Rc1/4	250 x 152	1.1
496-0106	TACP403-10	¥10,854	¥13,400	5	0.05 to 1.0	1.0	0.1 to 0.85	200	Rc3/8	250 x 152	1.1
496-0114	TACP403-15	¥10,854	¥13,400	5	0.05 to 1.0	1.5	0.1 to 0.85	200	Rc1/2	250 x 152	1.1

Contact us: 0120-509-849 <http://www.orange-book.com/>



TACP403-15



Stock 38,650 Items

FRL Unit (integrated type)



Features • A compact unit that integrates functions of the air filter, regulator, and lubricator on the same axis by employing a dual layered bottle.
Specs • Working fluid: Air • Fluid temperature: 5 to 60°C
 • Drain discharge method: Manual (however, automatically discharged when the pressure becomes 0.05MPa or less) • Working oil: Type 1 turbine oil (ISO VG#32 equivalent) • Pressure gauge with bracket
Origin • Taiwan

SPQ: 1 Piece

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Filtration Precision (μm)	Working Pressure (MPa)	Processing Air Volume (m ³ /min)	Set Pressure (MPa)	Oil Reservoir Capacity (cm ³)	Connection Port Diameter	Total Length (mm)	SPQ (piece)	Weight (kg)
254-9654	TP-25TOGB-8	¥7,290	¥9,000	5	1	0.7	0.05 to 0.85	50	Rc1/4	202.5	1	0.6
254-9662	TP-25TOGB-10	¥7,290	¥9,000	5	1	1.2	0.05 to 0.85	50	Rc3/8	202.5	1	0.6

Contact us: 0120-509-849 <http://www.orange-book.com/>



TP-25TOGB-8



Stock 38,650 Items

Filter Regulator



Features • Unit that integrates air filter and regulator.
Specs • Working fluid: Air • Fluid temperature: 5 to 60°C
 • Drain discharge method: Manual (however, automatically discharged when the pressure becomes 0.05MPa or less) • Pressure gauge with bracket
Origin • Taiwan

SPQ: 1 Piece

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Filtration Precision (μm)	Working Pressure (MPa)	Processing Air Volume (m ³ /min)	Set Pressure (MPa)	Connection Port Diameter	Total Length x Total Width (mm)	SPQ (piece)	Weight (kg)
496-0211	TAFR403-8	¥7,128	¥8,800	5	0.05 to 1.0	1.0	0.1 to 0.85	Rc1/4	250 x 72	1	0.62
496-0190	TAFR403-10	¥7,128	¥8,800	5	0.05 to 1.0	1.2	0.1 to 0.85	Rc3/8	250 x 72	1	0.62
496-0203	TAFR403-15	¥7,128	¥8,800	5	0.05 to 1.0	1.5	0.1 to 0.85	Rc1/2	250 x 72	1	0.62

Contact us: 0120-509-849 <http://www.orange-book.com/>



TAFR403-15



Stock 38,650 Items

Filter Regulator



Features • A compactly assembled equipment with integrated air filter and air regulator.
Specs • Working fluid: Air • Fluid temperature: 5 to 60°C
 • Drain discharge method: Manual (however, TP-3RTOFGB is automatically discharged when the pressure becomes 0.05MPa or less) • Pressure gauge with bracket
Origin • Taiwan

SPQ: 1 Piece

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Filtration Precision (μm)	Working Pressure (MPa)	Processing Air Volume (m ³ /min)	Set Pressure (MPa)	Connection Port Diameter	Total Length (mm)	SPQ (piece)	Weight (kg)
254-9611	TP-3R21FGB-8	¥5,443	¥6,720	40	1	0.5	0.05 to 0.85	Rc1/4	156.0	1	0.3
255-0237	TP-3RTOFGB-8	¥6,399	¥7,900	5	1	1.1	0.05 to 0.85	Rc1/4	206.5	1	0.4
255-0245	TP-3RTOFGB-10	¥6,399	¥7,900	5	1	1.3	0.05 to 0.85	Rc3/8	206.5	1	0.4

Contact us: 0120-509-849 <http://www.orange-book.com/>



TP-3RTOFGB-8