

Prices displayed include 8% tax.

TRUSCO **Stock 38,650 Items**

## Regulator



- Features**
- Adjust the air to a stable pressure.
- Specs**
- Working fluid: Air
  - Fluid temperature: 5 to 60°C
  - Pressure gauge with bracket
- Origin**
- Taiwan



TRUSCO NAKAYAMA CORPORATION

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Set Pressure (MPa)	Working Pressure (MPa)	Processing Air Volume (m <sup>3</sup> /min)	Connection Port Diameter	Total Length (mm)	SPQ (piece)	Weight (kg)
496-0271	TAR403-8	¥4,536	¥5,600	0.1 to 0.85	1	1.0	Rc1/4	129	1	0.45
496-0254	TAR403-10	¥4,536	¥5,600	0.1 to 0.85	1	1.2	Rc3/8	129	1	0.45
496-0262	TAR403-15	¥4,536	¥5,600	0.1 to 0.85	1	1.5	Rc1/2	129	1	0.45

Contact us: 0120-509-849 <http://www.orange-book.com/>



TRUSCO **Stock 38,650 Items**

## Regulator



- Features**
- Adjusts the air to be at a stable pressure.
  - A compact and mini type.
- Specs**
- Working fluid: Air
  - Fluid temperature: 5 to 60°C
  - Pressure gauge with bracket
- Origin**
- Taiwan




TRUSCO NAKAYAMA CORPORATION

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Set Pressure (MPa)	Working Pressure (MPa)	Processing Air Volume (m <sup>3</sup> /min)	Connection Port Diameter	Total Length (mm)	SPQ (piece)	Weight (kg)
254-9590	TP-3R21GB-8	¥3,321	¥4,100	0.05 to 0.85	1	0.6	Rc1/4	71.5	1	0.25

Contact us: 0120-509-849 <http://www.orange-book.com/>



TRUSCO **Stock 38,650 Items**

## Lubricator



- Features**
- Mix moderate amount of lubricant oil into the compressed air to make the pneumatic equipment smoother and prevent wear.
  - Lubricating oil dripping amount is adjustable with needle.
- Specs**
- Working fluid: Air
  - Fluid temperature: 5 to 60°C
  - Working oil: Type 1 turbine oil (ISO VG#32 equivalent)
- Origin**
- Taiwan



TRUSCO NAKAYAMA CORPORATION

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Working Pressure (MPa)	Processing Air Volume (m <sup>3</sup> /min)	Oil Reservoir Capacity (cm <sup>3</sup> )	Connection Port Diameter	Total Length (mm)	SPQ (piece)	Weight (kg)
496-0246	TAL403-8	¥3,888	¥4,800	1	1.2	200	Rc1/4	195	1	0.41
496-0220	TAL403-10	¥3,888	¥4,800	1	2.0	200	Rc3/8	195	1	0.41
496-0238	TAL403-15	¥3,888	¥4,800	1	2.1	200	Rc1/2	195	1	0.41

Contact us: 0120-509-849 <http://www.orange-book.com/>



TRUSCO **Stock 38,650 Items**

## Lubricator



- Features**
- Mix moderate amount of lubricant oil into the compressed air to make the pneumatic equipment smoother and prevent wear.
  - A compact and mini size.
  - Set after the regulator.
- Specs**
- Working fluid: Air
  - Fluid temperature: 5 to 60°C
  - Working oil: Type 1 turbine oil (ISO VG#32 equivalent)
- Origin**
- Taiwan



TRUSCO NAKAYAMA CORPORATION

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Working Pressure (MPa)	Processing Air Volume (m <sup>3</sup> /min)	Oil Reservoir Capacity (cm <sup>3</sup> )	Connection Port Diameter	Total Length (mm)	SPQ (piece)	Weight (kg)
254-9646	TP-2320-8	¥3,038	¥3,750	1	0.41	25	Rc1/4	116	1	0.3

Contact us: 0120-509-849 <http://www.orange-book.com/>



TRUSCO **Stock 38,650 Items**

## Air Filter



- Features**
- Eliminates moisture and dust from within the air by using centrifugal separation.
  - A compact and mini type.
- Specs**
- Working fluid: Air
  - Fluid temperature: 5 to 60°C
  - Drain discharge method: Manual
- Origin**
- Taiwan



TRUSCO NAKAYAMA CORPORATION

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Filtration Precision (μm)	Working Pressure (MPa)	Processing Air Volume (m <sup>3</sup> /min)	Connection Port Diameter	Total Length (mm)	SPQ (piece)	Weight (kg)
254-9581	TP-2720-8	¥2,365	¥2,920	40	1	0.39	Rc1/4	100	1	0.2

Contact us: 0120-509-849 <http://www.orange-book.com/>

