

Prices displayed include 8% tax.

For Drill Screwdrivers, see p. 5-124 to 156

TRUSCO
 Stock 38,650 Items

Adapter for Electric Screwdriver Powerful L-shaped Mini Pro



- Features**
- Supports powerful and hard work with a "compact body" & "18V compatibility."
 - Convenient for screw lock, removing and drilling in narrow corner and corner place.
 - A grip that can be held firmly and does not slip.
 - By adopting the lock type bit-holder, mounting of the double end drill bit becomes more secure and the 6.35mm hexagon shank drill bit can also be used.
 - Also compatible with 18V impact screwdrivers.
 - High precision powerful bearings are used.
- Materials**
- Special Steel
- Set Contents**
- Fixing Handle (bit storable)
 - $\oplus 2 \times 35$ (exclusive super short bit)
- Origin**
- Japan



Order Unit: 1 Set

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per set)	MSRP (per set)	Input Drive (mm)	Total Length x H (mm)	SPQ (set)	Weight (g/set)
819-1378	TDA-600	¥4,814	¥5,200	6.35	115 x 60	10	220

(when fixed handle is mounted)

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO
 Stock 38,650 Items

Adapter for Electric Screwdriver (L Type)



- Features**
- Convenient for screw lock, removing and drilling in narrow corner and corner place.
 - By adopting the lock type bit-holder, mounting of the double end drill bit becomes more secure and the 6.35mm hexagon shank drill bit can also be used.
 - Impact screwdriver is also available.
- Specs**
- Max Torque: 22N·m
- Set Contents**
- Fixed handle
 - Extension holder
 - \oplus No. 2 x 45 Double Headed Bit
- Origin**
- Japan



- Features**
- Convenient for screwing, removing, and drilling in narrow corners/edges. A grip that can be held firmly and does not slip.
 - By adopting the lock type bit-holder, mounting of the double end drill bit becomes more secure and the 6.35mm hexagon shank drill bit can also be used.
 - Impact screwdriver is also available.
- Specs**
- Maximum torque: 40N·m
- Set Contents**
- Fixed handle
 - \oplus No. 2 x 45 Double Headed Bit
- Origin**
- Japan

Order Unit: 1 Set

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per set)	MSRP (per set)	Input Drive (mm)	SPQ (set)	Weight (g/set)
270-9457	TDA-510	¥2,962	¥3,200	6.35	6	203

Contact us: 0120-509-849 <http://www.orange-book.com/>

Order Unit: 1 Set

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per set)	MSRP (per set)	Input Drive (mm)	SPQ (set)	Weight (g/set)
270-9465	TDA-550	¥4,814	¥5,200	6.35	3	460

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO

Super Slim Adapter for Electric Screwdriver (L Type)



- Features**
- A head width of 60mm (when \oplus No.2 x 35 exclusive super short bit is mounted).
 - Convenient for screwing, removing, and drilling in narrow corners/edges. A grip that can be held firmly and does not slip.
 - By adopting the lock type bit-holder, mounting of the double end drill bit becomes more secure and the 6.35mm hexagon shank drill bit can also be used.
 - Impact screwdriver is also available.
- Specs**
- Maximum torque: 60N·m
- Set Contents**
- Fixing Handle (bit storable)
 - $\oplus 2 \times 35$ (exclusive super short bit)
- Origin**
- Japan

ANEX
 Stock 823 Items

Tough Adapter (L Type)



- Features**
- Can use a socket bit, hole saw, and gimlet.
 - A replaceable shaft type that can be replaced even if the bit twists and snaps as a result of hard work.
 - A fixed handle type in which bits can be contained.
- Specs**
- Maximum torque: 110N·m
- Set Contents**
- Shaft size: 6.35mm
 - Fixing Handle (bit storable)
 - $\oplus 2 \times 35$ (single-ended bit)
 - $\oplus 2 \times 65$ (double-ended bit)
- Origin**
- Japan



Order Unit: 1 Set

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per set)	MSRP (per set)	Input Drive (mm)	SPQ (set)	Weight (g/set)
764-7638	TDA-570	¥4,814	¥5,200	6.35	10	282

Contact us: 0120-509-849 <http://www.orange-book.com/>

Order Unit: 1 Set

Kaneko Mfg Corporation

Order Code	Item No.	Price (per set)	MSRP (per set)	Input Drive (mm)	SPQ (set)	Weight (g/set)
469-6174	AKL-600	¥6,943	¥9,000	6.35	3	555

Contact us: 0256-32-6321 <http://www.anextool.co.jp/>