

# Air Micro Grinders

For Shank Mounted Whetstones, see p. 5-1095 to 1127

The number next to the logo mark indicates items in stock for each brand.

TRUSCO **Stock 38,650 Items** **Air Micro Grinders** Repairing OK



**TMAG10SN**  
(with a shank mounted stone)

- Features**
- Easy to grip, ergonomic design air micro grinder.
  - High precision air tool with excellent durability.
- Use**
- Burring, chamfering and polishing during various parts processing.
  - Molding die processing/glass processing.
  - For light grinding.
- Specs**
- Working Air Pressure: 0.4 to 0.6MPa
  - Accessories: Collet: 3.0mm (Item No.: 5028901)
- Origin**
- Japan



Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Chuck Inner Diameter (mm)	No Load Speed (min <sup>-1</sup> )	Air consumption (m <sup>3</sup> /min)	Hose Intake Port	Exhaust	Total Length (mm)	SPQ (piece)	Weight (g)
301-9128	TMAG10SN	¥20,250	¥25,000	3	60000	0.15	One Touch P Plug	Back	155	1	108

**Optional Parts**

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Applicable	SPQ (piece)	Weight (g)
497-1591	5028903	¥3,645	¥4,500	2.35mm Collet	20	1
497-1574	5028901	¥3,645	¥4,500	3.0mm Collet	20	1
497-1582	5028902	¥3,645	¥4,500	3.17mm Collet	20	1
497-1604	5028904	¥1,264	¥1,560	Collet Nut	20	1
818-7022	5025114	¥300	¥370	# 80 Pink Alundum Shank Mounted Whetstone (shaft diameter 3mm)	10	4

Contact us:0120-509-849 <http://www.orange-book.com/>



5025114  
(# 80 pink alundum shank mounted whetstone)

TRUSCO **Stock 38,650 Items** **Air Micro Grinders** Repairing OK



**TADT-1000**

- Features**
- High precision air tool with excellent durability.
  - Low vibration and high torque performance.
  - **Excellent cutting effect with ultra high speed rotation of 10000rpm.**
- Use**
- Burring and mold finishing during various parts processing.
  - Glass processing, metal processing and liquid crystal panel hole processing are possible.
- Specs**
- Working Air Pressure: 0.62MPa
  - Rotary Switch System
- Origin**
- Korea

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Chuck Inner Diameter (mm)	No Load Speed (min <sup>-1</sup> )	Air consumption (m <sup>3</sup> /min)	Hose Intake Port	Exhaust	Total Length (mm)	SPQ (piece)	Weight (g)
288-0059	TADT-1000	¥81,000	¥100,000	3	100000	0.2	R1/4	Back	145	1	250

Contact us:0120-509-849 <http://www.orange-book.com/>

UHT **Stock 128 Items** **Micro Hand Tool (new soft wrap accessory set)** Repairing OK



**MSG-3BSPLUST**

- Features**
- Adopts high performance motor realizing 55000rpm at air pressure of 0.4MPa and 65000rpm at air pressure of 0.6MPa.
  - Increase internal cooling fins to prevent heat generation.
- Use**
- Polishing of molds, processing of precision parts, deburring.
- Specs**
- Working Air Pressure: 0.4 to 0.6MPa
- Origin**
- Japan

Each sheet of 8 types of foil type new software wraps (with mounting bracket)

Item No.	Grain Size	Color	Item No.	Grain Size	Color
5150	#120	Black	5154	#600	Pink
5151	#240	Yellow	5155	#800	Purple
5152	#320	Green	5156	#1000	Brown
5153	#400	Orange	5157	#1500	Blue

One each of 8 types of shank mounted new soft wrap

Item No.	Grain Size	Color	Item No.	Grain Size	Color
5160	#120	Black	5164	#600	Pink
5161	#240	Yellow	5165	#800	Purple
5162	#320	Green	5166	#1000	Brown
5163	#400	Orange	5167	#1500	Blue



**Orange Book Limited**

Order Unit: 1 Piece

UHT CORP.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Chuck Inner Diameter (mm)	No Load Speed (min <sup>-1</sup> )	Air consumption (m <sup>3</sup> /min)	Hose Intake Port	Exhaust	Total Length (mm)	SPQ (piece)	Weight (g)
293-2385	MSG-3BSPLUST	¥35,438	¥35,000	3	65000	0.12 to 0.16	Quick Joint	Back	160.5	1	130

Contact us:0561-38-2101 <http://www.uht.co.jp/>