

Polishing Belts for Air Belt Sander

Stock 177 Items

5-549

Prices displayed include 8% tax.

TRUSCO Stock 38,650 Items


Adrasive Belt for Air Belt Sanders "957AT Small Belt"



- Features**
- Abrasive belt with 3M™ ceramic abrasive grain that is excellent in wear resistance.
 - Combines dramatic cutting power and long service life.
 - Flexible substrate is adopted.
 - A free-cutting material is applied to suppress heat generation and prevent burning of the object to be polished.
- Use**
- Grinding/polishing of difficult-to-cut materials such as stainless steel, nickel steel and titanium. (also demonstrates a similar performance in ordinary steel, carbon steel)
 - Bead Removal of Welding
 - Burring/chamfering.
- Materials**
- Whetstone: Ceramic Abrasive Grain
- Origin**
- Japan



957AT-10330: 80



957AT-10330:80 (front)

957AT-10330:80 (back)

Estimated Unit Price per Piece
¥122 to ¥182

Belts Dimension	Compatible Belt Sander
10 x 330mm	Nitto Kohki Belton (EBS-10, B-10N, BB-10A) Vessel (GT-B512) S. P. Air (SPS-37A) Kuken (KBS-12) Compact Tools (Z12A) Mine (NR-1115)
20 x 520mm	Nitto Kohki Belton (EBS-10, B-10N, BB-20) Vessel (GT-B520, GT-B520W) S. P. Air (SPS-38) Shinano (SI-2800) Compact Tools (220)



Example

Order Unit: 1 Box

(Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	OP	Price (per box)	MSRP (per box)	Grain Size (#)	W x L (mm)	Q'ty Per Box (piece)	SPQ (box)	Weight (g/box)
284-8325	957AT-10330	40	¥6,075	¥7,500	40	10 x 330	50	4	400
284-8333	957AT-10330	60	¥6,075	¥7,500	60	10 x 330	50	4	400
284-8341	957AT-10330	80	¥6,075	¥7,500	80	10 x 330	50	4	400
284-8350	957AT-10330	100	¥6,075	¥7,500	100	10 x 330	50	4	400
284-8368	957AT-10330	120	¥6,075	¥7,500	120	10 x 330	50	4	400
284-8376	957AT-20520	40	¥3,645	¥4,500	40	20 x 520	20	5	500
284-8384	957AT-20520	60	¥3,645	¥4,500	60	20 x 520	20	5	500
284-8392	957AT-20520	80	¥3,645	¥4,500	80	20 x 520	20	5	500
284-8406	957AT-20520	100	¥3,645	¥4,500	100	20 x 520	20	5	500
284-8414	957AT-20520	120	¥3,645	¥4,500	120	20 x 520	20	5	500

Contact us: 0120-509-849 <http://www.orange-book.com/>

NITTO KOHKI Stock 1,766 Items

Abrasive Belt for "Belton"



Abrasive Belt for BB-20

- Features**
- Efficient burring of various metals, rough scratching, surface grinding and polishing.
 - Grinding belts for Nitto Kohki genuine belton.
- Origin**
- Japan



Abrasive Belt (zirconia)



Abrasive Belt (ceramic)



Abrasive Belt (non-woven fabric)

Estimated Unit Price per Piece
¥129

Dedicated Polishing Belts (10mm)

Order Unit: 1 Box

(Price revision date: Oct, 2015) NITTO KOHKI Co.Ltd.

Order Code	Item No.	Price (per box)	MSRP (per box)	Grain Size (#)	Materials	Belt Dimension (mm)	Compatible Model	Q'ty Per Box (piece)	SPQ (box)	Weight (g/box)
209-8547	41461	¥6,453	¥6,830	Z60	Zirconia	10 x 330	BB-10A·B-10N·B-10CL·EBS-10	50	10	240
209-8571	41398	¥6,453	¥6,830	Z80	Zirconia	10 x 330	BB-10A·B-10N·B-10CL·EBS-10	50	10	220
209-8601	41397	¥6,453	¥6,830	Z100	Zirconia	10 x 330	BB-10A·B-10N·B-10CL·EBS-10	50	10	210
209-8636	41568	¥6,453	¥6,830	Z120	Zirconia	10 x 330	BB-10A·B-10N·B-10CL·EBS-10	50	10	180
209-8661	41570	¥6,453	¥6,830	Z180	Zirconia	10 x 330	BB-10A·B-10N·B-10CL·EBS-10	50	10	160
209-8695	41571	¥6,453	¥6,830	Z240	Zirconia	10 x 330	BB-10A·B-10N·B-10CL·EBS-10	50	10	150
209-8768	41407	¥6,453	¥6,830	AA400	Alumina	10 x 330	BB-10A·B-10N·B-10CL·EBS-10	50	10	170

Estimated Unit Price per Sheet
¥121 to ¥743

Dedicated Polishing Belts (20mm)

Order Unit: 1 Box

(Price revision date: Oct, 2015)

Order Code	Item No.	Price (per box)	MSRP (per box)	Grain Size (#)	Materials	Belt Dimension (mm)	Compatible Model	Q'ty Per Box (piece)	Weight (g/box)
276-1017	37515	¥2,417	¥2,560	Z60	Zirconia	20 x 330	BB-20	20	210
276-1025	37516	¥2,417	¥2,560	Z80	Zirconia	20 x 330	BB-20	20	190
276-1033	37517	¥2,417	¥2,560	Z100	Zirconia	20 x 330	BB-20	20	170
276-1041	37518	¥2,417	¥2,560	Z120	Zirconia	20 x 330	BB-20	20	160
276-1050	37519	¥2,417	¥2,560	Z180	Zirconia	20 x 330	BB-20	20	140
276-1068	37520	¥2,417	¥2,560	Z240	Zirconia	20 x 330	BB-20	20	130
276-1076	37521	¥2,417	¥2,560	A400	Alumina	20 x 330	BB-20	20	110
276-1084	37526	¥2,822	¥2,990	CE60	Ceramic	20 x 330	BB-20	20	230
276-1092	37527	¥2,822	¥2,990	CE80	Ceramic	20 x 330	BB-20	20	200
276-1106	37528	¥2,822	¥2,990	CE100	Ceramic	20 x 330	BB-20	20	170
276-1114	37529	¥2,822	¥2,990	CE120	Ceramic	20 x 330	BB-20	20	180
276-1122	37523	¥3,713	¥3,930	A	Non-woven Fabric	20 x 330	BB-20	5	90
276-1131	37522	¥3,713	¥3,930	A-VF	Non-woven Fabric	20 x 330	BB-20	5	80
276-1149	37524	¥3,713	¥3,930	S-SF	Non-woven Fabric	20 x 330	BB-20	5	80

Contact us: 0120-210-216 <http://www.nitto-kohki.co.jp/>

Pneumatic Tools

Air Impact Wrenches

Air Ratchet Wrenches

Air Screwdrivers

Air Drills

Air Micro Grinders

Air Grinders

Air Files

Air Sanders

Air Belt Sanders

Air Chisels

Air Hammers

Air Saws

Air Bevelers

Air Nippers

Air Dusters

Air Guns

Air Blast Machines