

Prices displayed include 8% tax.

TRUSCO **Stock 38,650 Items** **Stainless Nozzle for Air Duster** **RoHS**



22mm
TD-SUS-455

- Features**
- Can be used as countermeasures against contamination of foreign objects as it is stainless and strong resistance against rust.
 - Providing higher strength compared with conventional nozzles so that possibility of wear and breakage of the nozzle tip becomes low.
- Materials**
- Main body material: SUS304
- Origin**
- O-ring: Viton
 - Japan

SPQ: 10 Pieces

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Nozzle Length (mm)	Nozzle Opening Diameter (mm)	Nozzle Mounting Port	Weight (g)
764-8812	TD-SUS-455	¥3,703	¥4,000	22	2	G1/8	12

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items** **Air Duster Flexible Nozzle**



200mm
TD-18-FN200



300mm
TD-18-FN300



500mm
TD-18-FN500

- Features**
- Bending operation such as air blowing angle can be easily done by hand.
- Origin**
- Japan


SPQ: 10 Pieces

Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Nozzle Length (mm)	Nozzle Opening Diameter (mm)	Nozzle Mounting Port	Weight (g)
228-0701	TD-18-FN200	¥926	¥1,000	200	3	G1/8	18
228-0710	TD-18-FN300	¥1,047	¥1,130	300	3	G1/8	20
228-0728	TD-18-FN500	¥1,296	¥1,400	500	3	G1/8	25

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items** **Needle Nozzle for Air Duster**



95mm
TD-18-15N

- Features**
- Cutting chips can be removed by inserting the tip of the nozzle into the hole during processing such as tapping hole of 5mm or less.
- Origin**
- Japan

SPQ: 20 Pieces

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Nozzle Length (mm)	Nozzle Opening Diameter (mm)	Nozzle Mounting Port	Weight (g)
284-3811	TD-18-15N	¥1,990	¥2,150	95	1	G1/8	24

Contact us: 0120-509-849 <http://www.orange-book.com/>

KINKI **Stock 102 Items** **"Baby Freak Nozzle"**



KN-300BFF (flat nozzle)



300mm
KN-300BFR (round nozzle)

- Features**
- Ideal for air-blow at gaps and places that are hard to reach.
 - Silent, highly efficient, high flow rate long nozzle.
- Origin**
- Japan

SPQ: 1 Piece

Order Unit: 1 Piece (Price revision date: Apr, 2015) KINKI SEISAKUSYO

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Nozzle Length (mm)	Nozzle Opening Diameter (mm)	Nozzle Mounting Port	Weight (g)
363-1095	KN-300BFF	¥3,286	¥3,550	300	1.0 (x 8 pieces)	G1/8	108
363-1109	KN-300BFR	¥1,944	¥2,100	300	1.5 (x 8 pieces)	G1/8	136

Contact us: 06-6700-2601 <http://www.kinki-seisakusho.co.jp/>

TRUSCO **Stock 38,650 Items** **Air Duster Bent Nozzle**



145mm
TD-18-MN
Adjustment Nut


- Features**
- Suitable for dust work in a deep place such as the back of a machine.
- Origin**
- Japan

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Nozzle Length (mm)	Nozzle Opening Diameter (mm)	Nozzle Mounting Port	SPQ (piece)	Weight (g)
228-0698	TD-18-MN	¥602	¥650	145	2	G1/8	10	24

Contact us: 0120-509-849 <http://www.orange-book.com/>

KINKI **Stock 102 Items** **Bent Nozzle**



Nozzle Length
KN-35BT



KN-77BT

- Features**
- There is an angle at the tip so that the object can be aimed.
 - Nozzle that is frequently used.
- Origin**
- Japan

(Price revision date: Apr, 2015) KINKI SEISAKUSYO

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Nozzle Length (mm)	Nozzle Opening Diameter (mm)	Nozzle Mounting Port	SPQ (piece)	Weight (g)
413-3684	KN-35BT	¥2,083	¥2,250	350	3	G1/8	10	80
411-0315	KN-77BT	¥3,101	¥3,350	770	3	G1/8	10	156

Contact us: 06-6700-2601 <http://www.kinki-seisakusho.co.jp/>