

The number next to the logo mark indicates items in stock for each brand.

Welding Machines

Engine Welders

Spot Welders

Plasma Cutting Machines

Welding Tables

Welding Rods

Accessories for Welding Equipment

Welding Scale Removers

Gas Torches

Gas Burners

Gas Cutting Equipments

Gas Regulators

Brazing Filler Metals

Welding Masks

Protective Eyeweares for Welding

Protective Tools for Welding

Spatter Sheets

Protective Fences for Welding

Industrial Markers

TRUSCO **Stock 38,650 Items**

## Double Lens Shielding Glass RoHS

**.Com Drawing** Chemical Content Inspection OK with Glasses



GS-70W

- Features**
- It has high shading performance with upper and lower peak and sides.
  - Impact resistant Polycarbonate lens and UV cut.
- Specs**
- JIS T8141 standard product
- Materials**
- Frame: Plastic
  - Lens: Polycarbonate, hard coat
- Origin**
- Japan



- Warning**
- Shading degree #1.4 is for peripheral workers. (welding operators use #3)
  - Do not use as a shielding glass for laser light.
  - Do not use for arc welding.

Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Shielding Degree	SPQ (piece)	Weight (g)
284-7141	GS-70W-14	¥2,037	¥2,200	#1.4	10	37
126-3943	GS-70W	¥2,037	¥2,200	#3.0	10	37

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**

## Anti-fog Shielding Glasses

**.Com Drawing** Chemical Content Inspection OK with Glasses



TPK200-17

- Features**
- Glasses can be used together (excluding some large glasses).
  - Adopted double coating of tough coat that is resistant to scratch and less likely to get fogged.
  - Cuts UV rays by 99.9%.
  - ANSI Z87 + Compliant Product
- Use**
- For shielding of peripheral workers, and general dust proofing work.
- Materials**
- Polycarbonate (PC) / anti-fog coat
- Origin**
- Japan



- Warning**
- Cannot be used for work of ultraviolet ray lamp, etc.

Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Shielding Degree	SPQ (piece)	Weight (g)
484-6290	TPK200-17	¥3,666	¥3,960	#1.7 (ANSI)	10	50
484-6303	TPK200-25	¥3,666	¥3,960	#2.5 (ANSI)	10	50

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**

## Duplex-type Vertically-movable Shielding Glasses

**.Com Drawing** Chemical Content Inspection OK with Glasses



TDSG-G3

- Features**
- Adopting duplex-type lens (outer: shielding lens, inner: transparent lens), can also be used as protective glasses except as shielding glasses.
- Specs**
- JIS T8141 standard product
- Materials**
- Frame: Polycarbonate
- Origin**
- Japan

Item No.	Lens
TDSG-G	Tempered glass
TDSG-P	Polycarbonate

- Warning**
- Do not use as a shielding glass for laser light.
  - Do not use for arc welding.

Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Shielding Degree	SPQ (piece)	Weight (g)
484-7628	TDSG-G3	¥4,166	¥4,500	#3	30	69
783-9529	TDSG-G4	¥4,166	¥4,500	#4	30	69
484-7636	TDSG-P3	¥4,166	¥4,500	#3	30	57
783-9537	TDSG-P4	¥4,166	¥4,500	#4	30	57

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**

## Single Lens Shielding Glass RoHS

**.Com Drawing** Chemical Content Inspection OK with Glasses



GS-37W

- Features**
- UV-cut shielding lens excellent in scratch resistance.
  - Glasses can be used together. (excluding some large glasses)
- Use**
- For gas welding works.
- Materials**
- Frame: Polycarbonate (PC)
  - Lens: Polycarbonate (PC) / Hard Coating
- Origin**
- Japan



- Warning**
- Shading degree #1.4 is for peripheral workers. (welding operators use #3)
  - Do not use as a shielding glass for laser light.
  - Do not use for arc welding.

Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Shielding Degree	SPQ (piece)	Weight (g)
284-7132	GS-37W-14	¥1,666	¥1,800	#1.4	10	45
175-0101	GS-37W	¥1,666	¥1,800	#3.0	10	45

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**

## Single Lens Shielding Glass (over glass)

**.Com Drawing** Chemical Content Inspection OK with Glasses



TWG-17

- Features**
- UV-cut shielding lens excellent in scratch resistance.
  - Glasses can be used together. (excluding some large glasses)
  - You can adjust the angle of the shackle.
  - For gas welding works.
- Materials**
- Lens: Polycarbonate
  - Frame: Nylon
- Origin**
- Taiwan



- Warning**
- Shielding degree level #1.7 is for peripheral workers. (welding works operator uses #3)
  - Do not use as a shielding glass for laser light.
  - Do not use for arc welding.

Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Shielding Degree	SPQ (piece)	Weight (g)
445-6963	TWG-17	¥2,314	¥2,500	#1.7	30	45
445-6971	TWG-3	¥2,314	¥2,500	#3.0	30	45

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**

## Single Lens Shielding Glass RoHS

**.Com Drawing** Chemical Content Inspection OK with Glasses



TSG-71W

- Features**
- Shielding lens excellent in impact resistance.
  - Good with cushion bar per face.
  - Adjustable frame angle allows excellent fit.
- Use**
- For gas welding works.
- Materials**
- Frame: Polyamide
  - Lens: Polycarbonate (PC) / Hard Coating
- Origin**
- Japan

- Warning**
- Do not use as a shielding glass for laser light.
  - Do not use for arc welding.

Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Shielding Degree	SPQ (piece)	Weight (g)
288-0202	TSG-71W	¥3,518	¥3,800	#3	10	38

Contact us:0120-509-849 <http://www.orange-book.com/>