

Prices displayed include 8% tax.

For Partition Panels, see p. 10-178



Stock
38,650
Items

Catalogue Case (B4 type)



- Specs**
- Color: Neo Gray
 - Shallow Drawer: B4-20
 - Medium-deep type drawer: B4-15
 - Deep Type Drawer: B4-10
- Materials**
- Main Body: Steel
 - Drawer: PS resin
- Accessories**
- With each header card x 2Sheets for each drawer
- Origin**
- Japan

Warning
•Partition panel is sold separately.

Order Unit: 1 Piece | Factory direct | No freight charge | Excluding remote islands | (Price revision date: Jan, 2015) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Max Load Capacity (kg/piece)	W x D x H (mm)	Drawers (B4)			Drawers Effective Internal Dimension (mm) W x D x H	Weight (kg)
						Shallow Type	Medium Depth Type	Deep Type		
★504-5177	B1C10	¥33,974	¥36,700	30	315 x 400 x 880	-	-	1 row 10 stages	257 x 364 x 72	14.7
★504-5746	B1C15	¥38,510	¥41,600	30	315 x 400 x 880	-	1 row 15 stages	-	257 x 364 x 45	16.3
★504-6246	B1C20	¥41,935	¥45,300	30	315 x 400 x 880	1 row 20 stages	-	-	257 x 364 x 32	16.6



Order Unit: 1 Piece | Factory direct | No freight charge | Excluding remote islands | (Price revision date: Jan, 2015)

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Max Load Capacity (kg/piece)	W x D x H (mm)	Drawers (B4)			Drawers Effective Internal Dimension (mm) W x D x H	Weight (kg)
						Shallow Type	Medium Depth Type	Deep Type		
★504-5568	B2C10	¥62,208	¥67,200	50	600 x 400 x 880	-	-	2 rows 10 stages	257 x 364 x 72	26.5
★504-5916	B2C14	¥83,870	¥90,600	70	600 x 400 x 1200	-	-	2 rows 14 stages	257 x 364 x 72	36.2
★504-5924	B2C15	¥71,373	¥77,100	50	600 x 400 x 880	-	2 rows 15 stages	-	257 x 364 x 45	30.7
★504-6343	B2C20	¥79,334	¥85,700	50	600 x 400 x 880	2 rows 20 stages	-	-	257 x 364 x 32	30.0
★504-6033	B2C21	¥95,997	¥103,700	70	600 x 400 x 1200	-	2 rows 21 stages	-	257 x 364 x 45	40.0
★504-6041	B2C1015	¥68,040	¥73,500	50	600 x 400 x 880	-	1 row 15 stages	1 row 10 stages	257 x 364 x (medium-deep type/45, deep type/72)	32.5
★504-6181	B2C1020	¥71,465	¥77,200	50	600 x 400 x 880	1 row 20 stages	-	1 row 10 stages	257 x 364 x (shallow type/32, deep type/72)	32.8



Order Unit: 1 Piece | Factory direct | No freight charge | Excluding remote islands | (Price revision date: Jan, 2015)

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Max Load Capacity (kg/piece)	W x D x H (mm)	Drawers (B4)			Drawers Effective Internal Dimension (mm) W x D x H	Weight (kg)
						Shallow Type	Medium Depth Type	Deep Type		
★504-5720	B3C10	¥84,981	¥91,800	80	885 x 400 x 880	-	-	3 rows 10 stages	257 x 364 x 72	45.0
★504-5967	B3C15	¥99,514	¥107,500	80	885 x 400 x 880	-	3 rows 15 stages	-	257 x 364 x 45	48.0
★504-6386	B3C20	¥110,623	¥119,500	80	885 x 400 x 880	3 rows 20 stages	-	-	257 x 364 x 32	52.2
★508-0029	B3C834	¥97,107	¥104,900	75	880 x 400 x 880	3 rows 8 stages	3 rows 3 stages	3 rows 4 stages	257 x 364 x (shallow type 32, medium-deep type 45, deep type 72)	40.6

Contact us: 0120-509-849 <http://www.orange-book.com/>

- Desks
- PC Desks
- Meeting Tables
- Cafeteria Tables
- Office Chairs
- Meeting Chairs
- Working Chairs
- Anti-Static Stools
- Benches
- Umbrella Stands
- Reception Room Furnitures
- Hanger Racks
- Partitions
- Book Cabinets
- Counters
- Filing Cabinets
- Catalog Cases
- Map Cases/Letter Cases
- Pamphlet Stands
- File Wagons
- Lockers
- Shoes Boxes
- Safes
- Mailboxes
- Key Boxes
- Window Films
- Interior Blinds
- OA Floors
- System Kitchens