

**D8YU**  
(ピッチ : 8.0mm)

呼 称	ピッチ周長(mm)	歯数
512-D8YU	512.00	64
520-D8YU	520.00	65
536-D8YU	536.00	67
544-D8YU	544.00	68
552-D8YU	552.00	69
560-D8YU	560.00	70
576-D8YU	576.00	72
600-D8YU	600.00	75
608-D8YU	608.00	76
616-D8YU	616.00	77
624-D8YU	624.00	78
632-D8YU	632.00	79
640-D8YU	640.00	80
656-D8YU	656.00	82
664-D8YU	664.00	83
680-D8YU	680.00	85
704-D8YU	704.00	88
720-D8YU	720.00	90
728-D8YU	728.00	91
744-D8YU	744.00	93
752-D8YU	752.00	94
760-D8YU	760.00	95
768-D8YU	768.00	96
776-D8YU	776.00	97
784-D8YU	784.00	98
792-D8YU	792.00	99
800-D8YU	800.00	100
808-D8YU	808.00	101
816-D8YU	816.00	102
824-D8YU	824.00	103
832-D8YU	832.00	104
840-D8YU	840.00	105
848-D8YU	848.00	106
856-D8YU	856.00	107
864-D8YU	864.00	108
872-D8YU	872.00	109
880-D8YU	880.00	110
888-D8YU	888.00	111
896-D8YU	896.00	112
904-D8YU	904.00	113
912-D8YU	912.00	114
920-D8YU	920.00	115
928-D8YU	928.00	116
936-D8YU	936.00	117
944-D8YU	944.00	118
952-D8YU	952.00	119
960-D8YU	960.00	120
968-D8YU	968.00	121
976-D8YU	976.00	122
984-D8YU	984.00	123
992-D8YU	992.00	124
1000-D8YU	1000.00	125
1008-D8YU	1008.00	126
1016-D8YU	1016.00	127
1032-D8YU	1032.00	129
1040-D8YU	1040.00	130
1056-D8YU	1056.00	132
1064-D8YU	1064.00	133
1072-D8YU	1072.00	134
1080-D8YU	1080.00	135
1088-D8YU	1088.00	136
1096-D8YU	1096.00	137
1112-D8YU	1112.00	139
1120-D8YU	1120.00	140
1128-D8YU	1128.00	141
1136-D8YU	1136.00	142
1144-D8YU	1144.00	143
1152-D8YU	1152.00	144
1160-D8YU	1160.00	145
1168-D8YU	1168.00	146
1176-D8YU	1176.00	147
1184-D8YU	1184.00	148
1192-D8YU	1192.00	149
1200-D8YU	1200.00	150
1208-D8YU	1208.00	151

呼 称	ピッチ周長(mm)	歯数
1216-D8YU	1216.00	152
1224-D8YU	1224.00	153
1232-D8YU	1232.00	154
1240-D8YU	1240.00	155
1248-D8YU	1248.00	156
1256-D8YU	1256.00	157
1264-D8YU	1264.00	158
1272-D8YU	1272.00	159
1280-D8YU	1280.00	160
1288-D8YU	1288.00	161
1296-D8YU	1296.00	162
1304-D8YU	1304.00	163
1312-D8YU	1312.00	164
1320-D8YU	1320.00	165
1328-D8YU	1328.00	166
1336-D8YU	1336.00	167
1344-D8YU	1344.00	168
1352-D8YU	1352.00	169
1360-D8YU	1360.00	170
1376-D8YU	1376.00	172
1384-D8YU	1384.00	173
1392-D8YU	1392.00	174
1400-D8YU	1400.00	175
1408-D8YU	1408.00	176
1416-D8YU	1416.00	177
1424-D8YU	1424.00	178
1432-D8YU	1432.00	179
1440-D8YU	1440.00	180
1448-D8YU	1448.00	181
1456-D8YU	1456.00	182
1464-D8YU	1464.00	183
1480-D8YU	1480.00	185
1496-D8YU	1496.00	187
1520-D8YU	1520.00	190
1544-D8YU	1544.00	193
1568-D8YU	1568.00	196
1576-D8YU	1576.00	197
1600-D8YU	1600.00	200
1608-D8YU	1608.00	201
1616-D8YU	1616.00	202
1640-D8YU	1640.00	205
1656-D8YU	1656.00	207
1680-D8YU	1680.00	210
1688-D8YU	1688.00	211
1696-D8YU	1696.00	212
1720-D8YU	1720.00	215
1728-D8YU	1728.00	216
1736-D8YU	1736.00	217
1752-D8YU	1752.00	219
1760-D8YU	1760.00	220
1768-D8YU	1768.00	221
1776-D8YU	1776.00	222
1784-D8YU	1784.00	223
1800-D8YU	1800.00	225
1808-D8YU	1808.00	226
1816-D8YU	1816.00	227
1824-D8YU	1824.00	228
1856-D8YU	1856.00	232
1864-D8YU	1864.00	233
1872-D8YU	1872.00	234
1888-D8YU	1888.00	236
1896-D8YU	1896.00	237
1912-D8YU	1912.00	239
1928-D8YU	1928.00	241
1944-D8YU	1944.00	243
1952-D8YU	1952.00	244
1976-D8YU	1976.00	247
2000-D8YU	2000.00	250
2056-D8YU	2056.00	257
2072-D8YU	2072.00	259
2120-D8YU	2120.00	265
2136-D8YU	2136.00	267
2160-D8YU	2160.00	270
2240-D8YU	2240.00	280
2248-D8YU	2248.00	281

呼 称	ピッチ周長(mm)	歯数
2264-D8YU	2264.00	283
2280-D8YU	2280.00	285
2296-D8YU	2296.00	287
2304-D8YU	2304.00	288
2328-D8YU	2328.00	291
2368-D8YU	2368.00	296
2400-D8YU	2400.00	300
2456-D8YU	2456.00	307
2600-D8YU	2600.00	325
2800-D8YU	2800.00	350
2944-D8YU	2944.00	368
3200-D8YU	3200.00	400
3440-D8YU	3440.00	430
4400-D8YU	4400.00	550

■標準ベルト幅

ベルト幅(mm)
20.0
30.0
50.0
85.0

※ツインパワーベルトのベルト長さ許容差は、特殊公差になるため、当社までお問合わせください。