

MXLプーリ寸法表

下表は、標準在庫プーリ・受注生産プーリをご検討いただく際の参考寸法です。表以外の歯数・寸法のプーリも製作いたします。当社までお問い合わせください。

単位 mm

歯数	PD	OD	C(FID)	B	H	FOD	フランジ呼称
10	6.47	5.96	-	-	-	-	-
11	7.11	6.61	-	-	-	-	-
12	7.76	7.25	5.0	-	-	12	FA10012005
13	8.41	7.90	6.0	3	-	13	FA10013006
14	9.06	8.55	6.0	3	-	13	FA10013006
15	9.70	9.19	7.0	3	-	14	FA10014007
16	10.35	9.84	7.0	3	-	14	FA10014007
17	11.00	10.49	8.0	4	-	16	FA10016008
18	11.64	11.13	8.0	4	-	16	FA10016008
19	12.29	11.78	8.0	4	-	16	FA10016008
20	12.94	12.43	9.0	4	-	17	FA10017009
21	13.58	13.07	9.0	4	-	17	FA10017009
22	14.23	13.72	12.0	5	10	21	FA10021012
23	14.88	14.37	12.5	5	10	21	FA10021013
24	15.52	15.02	12.5	5	10	21	FA10021013
25	16.17	15.66	12.5	5	10	24	FA10024013
26	16.82	16.31	12.5	5	10	24	FA10024013
27	17.46	16.96	12.5	5	10	24	FA10024013
28	18.11	17.60	12.5	5	10	24	FA10024013
29	18.76	18.25	12.5	5	10	24	FA10024013
30	19.40	18.90	15.0	5	12	25	FA10025015
31	20.05	19.54	15.0	5	12	25	FA10025015
32	20.70	20.19	15.0	5	12	25	FA10025015
33	21.34	20.84	17.5	6	14	28	FA10028018
34	21.99	21.48	17.5	6	14	28	FA10028018
35	22.64	22.13	17.5	6	14	28	FA10028018
36	23.29	22.78	17.5	6	14	28	FA10028018
37	23.93	23.42	20.0	6	16	30	FA10030020
38	24.58	24.07	20.0	6	16	30	FA10030020
39	25.23	24.72	20.0	6	16	30	FA10030020
40	25.87	25.36	20.0	6	16	32	FA10032020
41	26.52	26.01	20.0	6	16	32	FA10032020
42	27.17	26.66	22.5	6	18	33	FA10033023
43	27.81	27.30	22.5	6	18	33	FA10033023
44	28.46	27.95	25.0	6	20	35	FA10035025
45	29.11	28.60	25.0	6	20	35	FA10035025
46	29.75	29.25	25.0	6	20	35	FA10035025
47	30.40	29.89	25.0	6	20	35	FA10035025
48	31.05	30.54	27.5	8	22	40	FA10040028
49	31.69	31.19	27.5	8	22	40	FA10040028
50	32.34	31.83	27.5	8	22	40	FA10040028
51	32.99	32.48	27.5	8	22	40	FA10040028
52	33.63	33.13	27.5	8	22	40	FA10040028
53	34.28	33.77	27.5	8	22	40	FA10040028
54	34.93	34.42	27.5	8	22	40	FA10040028
55	35.57	35.07	31.0	8	26	45	FA10045031
56	36.22	35.71	31.0	8	26	45	FA10045031
57	36.87	36.36	31.0	8	26	45	FA10045031
58	37.51	37.01	31.0	8	26	45	FA10045031
59	38.16	37.65	31.0	8	26	45	FA10045031
60	38.81	38.30	31.0	8	26	45	FA10045031
61	39.46	38.95	31.0	8	26	45	FA10045031
62	40.10	39.59	31.0	8	26	45	FA10045031
63	40.75	40.24	36.0	10	30	48	FA10048036
64	41.40	40.89	36.0	10	30	48	FA10048036
65	42.04	41.53	36.0	10	30	48	FA10048036
66	42.69	42.18	36.0	10	30	48	FA10048036
67	43.34	42.83	36.0	10	30	48	FA10048036
68	43.98	43.47	36.0	10	30	52	FA10052036
69	44.63	44.12	36.0	10	30	52	FA10052036
70	45.28	44.77	36.0	10	30	52	FA10052036
71	45.92	45.42	36.0	10	30	52	FA10052036
72	46.57	46.06	36.0	10	30	52	FA10052036
73	47.22	46.71	41.0	10	32	55	FA10055041
74	47.86	47.36	41.0	10	32	55	FA10055041
75	48.51	48.00	41.0	10	32	55	FA10055041
76	49.16	48.65	41.0	10	32	55	FA10055041
77	49.80	49.30	41.0	10	32	55	FA10055041
78	50.45	49.94	46.0	10	34	58	FA10058046
79	51.10	50.59	46.0	12	34	58	FA10058046
80	51.74	51.24	46.0	12	34	58	FA10058046

歯数	PD	OD	C(FID)	B	H	FOD	フランジ呼称
81	52.39	51.88	46.0	12	34	58	FA10058046
82	53.04	52.53	46.0	12	34	58	FA10058046
83	53.68	53.18	46.0	12	34	61	FA10061046
84	54.33	53.82	46.0	12	34	61	FA10061046
85	54.98	54.47	46.0	12	34	61	FA10061046
86	55.63	55.12	46.0	12	34	61	FA10061046
87	56.27	55.76	51.0	12	36	67	FA10067051
88	56.92	56.41	51.0	12	36	67	FA10067051
89	57.57	57.06	51.0	12	36	67	FA10067051
90	58.21	57.70	51.0	12	36	67	FA10067051
91	58.86	58.35	51.0	12	36	67	FA10067051
92	59.51	59.00	51.0	12	36	67	FA10067051
93	60.15	59.64	51.0	12	36	67	FA10067051
94	60.80	60.29	51.0	12	36	67	FA10067051
95	61.45	60.94	51.0	12	36	67	FA10067051
96	62.09	61.59	51.0	12	36	67	FA10067051
97	62.74	62.23	56.0	12	38	70	FA10070056
98	63.39	62.88	56.0	12	38	70	FA10070056
99	64.03	63.53	56.0	12	38	70	FA10070056
100	64.68	64.17	56.0	12	38	70	FA10070056
101	65.33	64.82	56.0	12	38	70	FA10070056
102	65.97	65.47	61.0	12	40	76	FA10076061
103	66.62	66.11	61.0	12	40	76	FA10076061
104	67.27	66.76	61.0	12	40	76	FA10076061
105	67.91	67.41	61.0	12	40	76	FA10076061
106	68.56	68.05	61.0	12	40	76	FA10076061
107	69.21	68.70	61.0	12	40	76	FA10076061
108	69.86	69.35	65.0	12	44	77	FA10077065
109	70.50	69.99	65.0	12	44	77	FA10077065
110	71.15	70.64	65.0	12	44	77	FA10077065
111	71.80	71.29	65.0	12	44	77	FA10077065
112	72.44	71.93	65.0	12	44	77	FA10077065
113	73.09	72.58	66.0	12	48	83	FA10083066
114	73.74	73.23	66.0	12	48	83	FA10083066
115	74.38	73.87	66.0	12	48	83	FA10083066
116	75.03	74.52	66.0	12	48	83	FA10083066
117	75.68	75.17	66.0	12	48	83	FA10083066
118	76.32	75.82	66.0	12	48	83	FA10083066
119	76.97	76.46	66.0	12	48	83	FA10083066
120	77.62	77.11	66.0	12	48	83	FA10083066
121	78.26	77.76	74.0	12	52	86	FA10086074
122	78.91	78.40	74.0	12	52	86	FA10086074
123	79.56	79.05	74.0	12	52	86	FA10086074
124	80.20	79.70	74.0	12	52	86	FA10086074
125	80.85	80.34	74.0	12	52	86	FA10086074
126	81.50	80.99	74.0	12	52	86	FA10086074
127	82.14	81.64	74.0	12	52	86	FA10086074
128	82.79	82.28	77.0	12	58	90	FA10090077
129	83.44	82.93	77.0	12	58	90	FA10090077
130	84.08	83.58	77.0	12	58	90	FA10090077
131	84.73	84.22	77.0	12	58	90	FA10090077
132	85.38	84.87	77.0	12	58	90	FA10090077
133	86.03	85.52	81.0	12	62	93	FA10093081
134	86.67	86.16	81.0	12	62	93	FA10093081
135	87.32	86.81	81.0	12	62	93	FA10093081
136	87.97	87.46	81.0	12	62	93	FA10093081
137	88.61	88.10	84.0	12	62	96	FA12096084
138	89.26	88.75	84.0	12	62	96	FA12096084
139	89.91	89.40	84.0	12	62	96	FA12096084
140	90.55	90.04	84.0	12	62	96	FA12096084
141	91.20	90.69	84.0	12	62	96	FA12096084
142	91.85	91.34	84.0	12	62	96	FA12096084
143	92.49	91.99	87.0	12	66	99	FA12099087
144	93.14	92.63	87.0	12	66	99	FA12099087
145	93.79	93.28	87.0	12	66	99	FA12099087
146	94.43	93.93	87.0	12	66	99	FA12099087
147	95.08	94.57	87.0	12	66	99	FA12099087
148	95.73	95.22	90.0	12	72	102	FA12102090
149	96.37	95.87	90.0	12	72	102	FA12102090
150	97.02	96.51	90.0	12	72	102	FA12102090

は標準在庫プーリもご用意しております。形状については、132ページをご参照ください。