

Lプーリ寸法表

下表は、標準在庫プーリ・受注生産プーリをご検討いただく際の参考寸法です。表以外の歯数・寸法のプーリも製作いたします。当社までお問い合わせください。

単位 mm

歯数	PD	OD	C(FID)	B	H	M	FOD	フランジ呼称
10	30.32	29.56	25.0	7	21	-	35	FS15035025
11	33.35	32.59	27.5	7	21	-	40	FS15040028
12	36.38	35.62	31.0	8	27	-	45	FS15045031
13	39.41	38.65	31.0	8	27	-	45	FS15045031
14	42.45	41.68	36.0	10	30	-	48	FS15048036
15	45.48	44.72	36.0	10	32	-	52	FS15052036
16	48.51	47.75	41.0	12	34	-	55	FS15055041
17	51.54	50.78	46.0	12	34	-	58	FS15058046
18	54.57	53.81	46.0	12	36	-	61	FS15061046
19	57.61	56.84	51.0	12	37	-	67	FS15067051
20	60.64	59.88	51.0	12	38	-	67	FS15067051
21	63.67	62.91	56.0	12	39	-	70	FS15070056
22	66.70	65.94	61.0	12	40	-	76	FS15076061
23	69.73	68.97	61.0	12	40	-	76	FS15076061
24	72.77	72.00	66.0	12	42	-	83	FS15083066
25	75.80	75.04	66.0	12	42	-	83	FS15083066
26	78.83	78.07	71.0	12	42	-	88	FS15088071
27	81.86	81.10	71.0	12	42	-	88	FS15088071
28	84.89	84.13	75.0	12	44	-	95	FS15095075
29	87.93	87.16	75.0	12	44	-	95	FS15095075
30	90.96	90.20	80.0	12	44	-	99	FS15099080
31	93.99	93.23	85.0	12	44	-	103	FS15103085
32	97.02	96.26	85.0	16	46	-	103	FS15103085
33	100.05	99.29	90.0	16	46	-	111	FS15111090
34	103.08	102.32	95.0	16	46	-	115	FS15115095
35	106.12	105.35	95.0	16	46	-	115	FS15115095
36	109.15	108.39	100.0	16	48	-	119	FS15119100
37	112.18	111.42	100.0	16	48	-	119	FS15119100
38	115.21	114.45	105.0	16	50	-	123	FS15123105
39	118.24	117.48	105.0	16	50	-	127	FS15127105
40	121.28	120.51	110.0	16	50	-	131	FS15131110
41	124.31	123.55	115.0	16	50	-	135	FS15135115
42	127.34	126.58	115.0	16	50	-	135	FS15135115
43	130.37	129.61	120.0	16	50	-	140	FS15140120
44	133.40	132.64	120.0	16	52	109	140	FS15140120
45	136.44	135.67	125.0	16	52	112	144	FS15144125
46	139.47	138.71	125.0	16	52	115	148	FS20148125
47	142.50	141.74	130.0	16	52	118	152	FS15152130
48	145.53	144.77	130.0	16	52	121	152	FS15152130
49	148.56	147.80	135.0	16	52	123	156	-
50	151.60	150.83	140.0	16	52	125	160	-
51	154.63	153.86	140.0	16	52	128	160	-
52	157.66	156.90	145.0	16	52	131	168	-
53	160.69	159.93	145.0	16	52	135	168	-
54	163.72	162.96	150.0	16	52	138	172	-
55	166.75	165.99	150.0	16	56	141	172	-
56	169.79	169.02	155.0	16	56	144	176	-
57	172.82	172.06	155.0	16	56	147	180	-
58	175.85	175.09	160.0	16	56	150	184	-
59	178.88	178.12	165.0	16	56	153	188	-
60	181.91	181.15	165.0	16	56	156	188	FS20188165
61	184.95	184.18	170.0	16	56	159	192	-
62	187.98	187.22	170.0	20	60	162	196	-
63	191.01	190.25	170.0	20	60	165	196	-
64	194.04	193.28	175.0	20	60	168	200	-
65	197.07	196.31	181.0	20	60	171	203	-

歯数	PD	OD	C(FID)	B	H	M	FOD	フランジ呼称
66	200.11	199.34	184.0	20	60	174	206	-
67	203.14	202.38	186.0	20	60	177	209	-
68	206.17	205.41	189.0	20	60	180	212	-
69	209.20	208.44	192.0	20	60	183	215	-
70	212.23	211.47	195.0	20	60	185	218	-
71	215.27	214.50	198.0	20	60	187	221	-
72	218.30	217.53	201.0	20	60	190	225	FS20225201
73	221.33	220.57	204.0	20	64	193	228	-
74	224.36	223.60	207.0	20	64	195	231	-
75	227.39	226.63	210.0	20	64	199	234	-
76	230.42	229.66	212.0	20	64	201	237	-
77	233.46	232.69	215.0	20	64	205	240	-
78	236.49	235.73	218.0	20	64	208	243	-
79	239.52	238.76	221.0	20	64	210	246	-
80	242.55	241.79	224.0	20	72	214	249	-
81	245.58	244.82	227.0	20	72	217	252	-
82	248.62	247.85	230.0	20	72	220	255	-
83	251.65	250.89	233.0	25	72	223	258	-
84	254.68	253.92	236.0	25	72	226	261	-
85	257.71	256.95	239.0	25	72	229	264	-
86	260.74	259.98	242.0	25	72	232	267	-
87	263.78	263.01	245.0	25	72	235	270	-
88	266.81	266.05	248.0	25	80	238	273	-
89	269.84	269.08	251.0	25	80	241	276	-
90	272.87	272.11	254.0	25	80	244	279	-
91	275.90	275.14	257.0	25	80	247	282	-
92	278.93	278.17	260.0	25	80	250	285	-
93	281.97	281.20	263.0	25	80	253	288	-
94	285.00	284.24	266.0	25	80	256	291	-
95	288.03	287.27	269.0	25	80	259	294	-
96	291.06	290.30	272.0	25	80	262	297	-
97	294.09	293.33	275.0	25	80	265	300	-
98	297.13	296.36	278.0	25	80	268	303	-
99	300.16	299.40	281.0	25	80	271	306	-
100	303.19	302.43	284.0	30	82	274	309	-
101	306.22	305.46	287.0	30	82	277	312	-
102	309.25	308.49	290.0	30	82	280	315	-
103	312.29	311.52	293.0	30	82	283	318	-
104	315.32	314.56	296.0	30	82	286	321	-
105	318.35	317.59	299.0	30	82	289	324	-
106	321.38	320.62	302.0	30	82	292	327	-
107	324.41	323.65	305.0	30	82	295	330	-
108	327.45	326.68	308.0	30	82	298	333	-
109	330.48	329.72	311.0	30	82	301	336	-
110	333.51	332.75	314.0	30	84	304	339	-
111	336.54	335.78	317.0	30	84	307	342	-
112	339.57	338.81	320.0	30	84	310	345	-
113	342.60	341.84	323.0	30	84	313	348	-
114	345.64	344.87	326.0	30	84	316	351	-
115	348.67	347.91	329.0	30	84	319	354	-
116	351.70	350.94	332.0	30	84	322	357	-
117	354.73	353.97	335.0	30	84	325	360	-
118	357.76	357.00	339.0	30	84	329	364	-
119	360.80	360.03	342.0	30	84	332	367	-
120	363.83	363.07	-	-	-	-	-	-

□ は標準在庫プーリもご用意しております。形状については、136ページをご参照ください。

標準在庫プーリのB寸法は、下穴寸法を記載しております。