


Standard Linear Ball Bearing Steel Drawn Cup/Cage Plastic



**Dimensions
[mm]**

**Load Capacity
[N]**

**Weight
[g]**

Part-No.	ϕd	ϕD	B	Dyn.	Stat.	
KH-0622	6	12	22	400	240	7
KH-0824	8	15	24	440	280	12
KH-1026	10	17	26	500	370	14.5
KH-1228	12	19	28	620	510	18.5
KH-1428	14	21	28	710	530	20.5
KH-1630	16	24	30	800	630	27.5
KH-2030	20	28	30	950	800	32.5
KH-2540	25	35	40	1990	1560	66
KH-3050	30	40	50	2900	2700	95
KH-4060	40	52	60	5100	4500	182
KH-5070	50	62	70	6950	6300	252

Ordering Example:

