


LMHP...LUU尼龙保持架
该类型尺寸是公制的，广泛应用于亚洲和其他国家。

LMHP...LUU (Resin retainer)
This type is a metric dimension series widely used in Asia and other countries.



LMHP...LUU

公称轴径 Nominal shaft diameter mm	加长导向椭圆法兰 LMHP...LUU	重量 Weight (gf)	主要尺寸和公差 Major dimensions and tolerance					
			dr		D		L	
			mm	公差 Tolerance μm	mm	公差 Tolerance μm	mm	公差 Tolerance μm
6	LMHP6LUU	28	6	0	12	0	35	± 300
8	LMHP8LUU	47	8		15	-13	45	
10	LMHP10LUU	90	10		19	0	55	
12	LMHP12LUU	102	12	-10	21	0	57	0
13	LMHP13LUU	123	13		23	-16	61	
16	LMHP16LUU	182	16		28	0	70	
20	LMHP20LUU	247	20	0	32	0	80	-300
25	LMHP25LUU	525	25		40	-19	112	
30	LMHP30LUU	645	30		45	0	123	

注：所有LMHP...L型均为双密封。
Note: All sizes of LMHP...L type are sealed on both sides.