

**For CM-10 modules and ConCept system bus, 1 and 4 poles**

**Crimp contacts**


Surface Gold



Surface Silver



Qty.	Male	Order No.	Female	Order No.
100	HDC-C-HD-SM0.14-0.37AU	<b>1651620000</b>	HDC-C-HD-BM0.14-0.37AU	<b>1651670000</b>
100	HDC-C-HD-SM0.5AU	<b>1651630000</b>	HDC-C-HD-BM0.5AU	<b>1651680000</b>
100	HDC-C-HD-SM0.75-1.00AU	<b>1651640000</b>	HDC-C-HD-BM0.75-1.00AU	<b>1651690000</b>
100	HDC-C-HD-SM1.5AU	<b>1651650000</b>	HDC-C-HD-BM1.5AU	<b>1651700000</b>
100	HDC-C-HD-SM2.5AU	<b>1651660000</b>	HDC-C-HD-BM2.5AU	<b>1651710000</b>
100	HDC-C-HD-SM0.14-0.37AG	<b>1651520000</b>	HDC-C-HD-BM0.14-0.37AG	<b>1651570000</b>
100	HDC-C-HD-SM0.5AG	<b>1651530000</b>	HDC-C-HD-BM0.5AG	<b>1651580000</b>
100	HDC-C-HD-SM0.75-1.00AG	<b>1601750000</b>	HDC-C-HD-BM0.75-1.00AG	<b>1601760000</b>
100	HDC-C-HD-SM1.5AG	<b>1651550000</b>	HDC-C-HD-BM1.5AG	<b>1651600000</b>
100	HDC-C-HD-SM2.5AG	<b>1651560000</b>	HDC-C-HD-BM2.5AG	<b>1651610000</b>



Conductor cross-section	Insulation stripping length
0.14 – 0.37 mm <sup>2</sup>	AWG 26-22 8 mm
0.50 mm <sup>2</sup>	AWG 20 8 mm
0.75 – 1.00 mm <sup>2</sup>	AWG 18 8 mm
1.50 mm <sup>2</sup>	AWG 16 8 mm
2.50 mm <sup>2</sup>	AWG 14 8 mm

**Tools**



Crimping tool	Order No.
CTX CM 1.6 / 2.5	<b>9018490000</b>
CTIN CM 1.6/2.5	<b>9205430000</b>
Contact release tool	Order No.
Removal Tool HD	<b>1866730000</b>

**For CM-HE modules and ConCept system bus, 1-pole HE**

**Crimp contacts**

Surface Gold



Surface Silver



Qty.	Male	Order No.	Female	Order No.
100	HDC-C-HE-SM0.5AU	<b>1651420000</b>	HDC-C-HE-BM0.5AU	<b>1651470000</b>
100	HDC-C-HE-SM0.75-1.00AU	<b>1651430000</b>	HDC-C-HE-BM0.75-1.00AU	<b>1651480000</b>
100	HDC-C-HE-SM1.5AU	<b>1651440000</b>	HDC-C-HE-BM1.5AU	<b>1651490000</b>
100	HDC-C-HE-SM2.5AU	<b>1651450000</b>	HDC-C-HE-BM2.5AU	<b>1651500000</b>
100	HDC-C-HE-SM4.0AU	<b>1651460000</b>	HDC-C-HE-BM4.0AU	<b>1651510000</b>
100	HDC-C-HE-SM4.65AU	<b>1116540000</b>	HDC-C-HE-BM4.65AU	<b>1116530000</b>
100	HDC-C-HE-SM0.5AG	<b>1200500000</b>	HDC-C-HE-BM0.5AG	<b>1201100000</b>
100	HDC-C-HE-SM0.75-1.00AG	<b>1200600000</b>	HDC-C-HE-BM0.75-1.00AG	<b>1201200000</b>
100	HDC-C-HE-SM1.5AG	<b>1200700000</b>	HDC-C-HE-BM1.5AG	<b>1201300000</b>
100	HDC-C-HE-SM2.5AG	<b>1200800000</b>	HDC-C-HE-BM2.5AG	<b>1201400000</b>
100	HDC-C-HE-SM4.0AG	<b>1200900000</b>	HDC-C-HE-BM4.0AG	<b>1201500000</b>



Conductor cross-section	Insulation stripping length
0.50 mm <sup>2</sup>	AWG 20 7.5 mm
0.75 – 1.00 mm <sup>2</sup>	AWG 18 7.5 mm
1.50 mm <sup>2</sup>	AWG 16 7.5 mm
2.50 mm <sup>2</sup>	AWG 14 7.5 mm
4.00 mm <sup>2</sup>	AWG 12 7.5 mm
4.65 mm <sup>2</sup>	AWG 11 7.5 mm

**Tools**



Crimping tool	Order No.
CTX CM 1.6 / 2.5	<b>9018490000</b>
CTIN CM 1.6/2.5	<b>9205430000</b>
Contact release tool	Order No.
Removal Tool HD	<b>1866750000</b>

**For ConCept ST modules with hybrid insert**

**Crimp contacts hybrid**


Male



Female



Qty.	Male	Order No.	Female	Order No.
300	IE-BIC-HYB-P-0.5-300	<b>1096150000</b>	IE-PIC-HYB-S-0.5-300	<b>1096180000</b>



Conductor cross-section	Insulation stripping length
0.21 – 0.50 mm <sup>2</sup>	AWG 24-20 3.5 mm

**Accessories**



Crimping tool hybrid	Order No.
HTF HYB	<b>1119580000</b>