


# 1100


Oリングポート オス コネクター  
O-Ring port male connector  
External pipe/JIS O-Ring boss (internal)



呼称サイズ	T <sub>1</sub>	T <sub>2</sub>	A	X
02-04	1/8	1/4	33	19
04	1/4	1/4	36	19
04-06	1/4	3/8	35	22
06	3/8	3/8	37	22
06-04	3/8	1/4	37	19
06-08	3/8	1/2	43	27
08	1/2	1/2	46	27
08-06	1/2	3/8	40	22
08-12	1/2	3/4	48	36
12	3/4	3/4	50	36
12-08	3/4	1/2	48	27
12-16	3/4	1	55	41
16	1	1	57	41
16-12	1	3/4	52	36

# 1068


Oリングボス メス コネクター  
O-Ring boss female connector  
Internal pipe/JIS O-Ring boss



呼称サイズ	T <sub>1</sub>	T <sub>2</sub>	A	X
04	1/4	1/4	28	19
04-02	1/4	1/8	28	19
04-06	1/4	3/8	30	22
06	3/8	3/8	31	22
06-04	3/8	1/4	31	22
06-08	3/8	1/2	37	27
08	1/2	1/2	40	27
08-06	1/2	3/8	40	27
08-12	1/2	3/4	40.5	36
12	3/4	3/4	42	36
12-08	3/4	1/2	42	36
12-16	3/4	1	46.5	41
16	1	1	49	41
16-12	1	3/4	49	41

# 1106

Oリングボス オス 45° エルボ  
O-Ring boss (adj) male 45° elbow  
External pipe/JIS O-Ring boss (adj)



呼称サイズ	T <sub>1</sub>	T <sub>2</sub>	A	B
04	1/4	1/4	29	21
06	3/8	3/8	33	25
08	1/2	1/2	39	28
12	3/4	3/4	44	33
16	1	1	47	37