



1067 オス コネクター
Male connector
JIS O-Ring boss/PF30° MIS




呼称サイズ	T ₁	T ₂	A	X
02	1/8	1/8	29	17
04	1/4	1/4	33	19
04-06	1/4	3/8	34	19
04-08	1/4	1/2	38	22
06	3/8	3/8	36	22
06-04	3/8	1/4	38	22
06-08	3/8	1/2	45	22
06-12	3/8	3/4	42	27
08	1/2	1/2	42	27
08-04	1/2	1/4	35	27
08-06	1/2	3/8	40	27
08-12	1/2	3/4	45	30
12	3/4	3/4	49	36
12-06	3/4	3/8	43	36
12-08	3/4	1/2	46	36
12-16	3/4	1	50	36
16	1	1	58	41
16-08	1	1/2	50	41
16-12	1	3/4	52	41

1067-□A オス ロング コネクター
Male long connector
JIS O-Ring boss/PF30° MIS



呼称サイズ	T ₁	T ₂	A	X
04-105A	1/4	1/4	105	19
06-87A	3/8	3/8	87	22
08-62A	1/2	1/2	62	27
08-12-70A	1/2	3/4	70	30

1072 オス45° 座付エルボ
Male 45° O-Ring boss (adj) elbow
JIS O-Ring boss (adj)/PF30° MIS



呼称サイズ	T ₁	T ₂	A	B
04	1/4	1/4	29	19
04-06	1/4	3/8	33	24
06	3/8	3/8	33	24
06-04	3/8	1/4	33	24
06-08	3/8	1/2	39	28
08	1/2	1/2	39	28
08-06	1/2	3/8	39	28
08-12	1/2	3/4	44	32
12	3/4	3/4	44	32
12-08	3/4	1/2	44	32
12-16	3/4	1	47	37
16	1	1	47	37
16-12	1	3/4	47	37