

Components for Inspection

Components for Inspection and Locating Kits, Construction Balls, Pads, Covers

■ **Features:** For locating removable jig parts. (See app. example below)

■ **Components for Inspection and Locating Kits** RoHS10

Config.		Type	Material, Hardness, Surface Treatment			
Knurling of Collar / Bushing	Stripper Bolt Shape		Collar / Bushing	Stripper Bolt	Wing Screw Type only	
Provided	Hex Socket Head With Wing Screw	KJLP	SS400	SCM435 33-38HRC	SS400 Trivalent Chromate	Spring Steel 45-50HRC
Not Provided	Hex Socket Head	KJLPC				
	Hex Socket Head With Wing Screw	KJLPNC				

* If only shoulder bolts for wrench are required, order GMSB (P. 2-216).

• **Bushing**
*Tolerance is applicable only with no Knurling.

• **Collar**
*Stripper Bolt (Hex Socket Head)

(With Wing Screw)

Part Number		D	L	Stripper Bolt									Wing Screw		Unit Price			
Type				P	M	f	F	ℓ	E	A	B	h	d	KJLP	KJLPC	KJLPN	KJLPNC	
KJLP KJLPN	KJLPC KJLPNC	12	15	6	M4	6	7	30	4	9	3	15	21					
			25	6	M4	6	7	40	4	9	3	15	21					
			20	15	10	M8	8	12	25	8	16	6	24	31				
			30	10	M8	8	12	40	8	16	6	24	31					

Ordering Example: Part Number - L
KJLP20 - 15

Alterations: Part Number - L - (HT, STC)
KJLP20 - 15 - HT

Alterations	Code	Spec.
Plats Machining	HT	Chamfers a side of collar and bushing.
Additional Surface Treatment (Black Oxide)	STC	Adds black oxide surface treatment. *Applicable to collar and bushing only.

Construction Balls

CRB

Material: SUS440C
Hardness: HRC56

Part Number Type	P	T	D	(L)	L ₁	d	Unit Price	
							1 ~ 49 pc(s)	50-100 pcs.
CRB	12	10	6	25.73	15.723	2.03		
	20	20	10	43	23	3		

* Product CRB12 is shipped if P dimension isn't specified.

Example: Inspection Component

For Accuracy Control of Inspection Components.

Pads for Construction Balls

CRBP

Material: SS400
Surface Treatment: Black Oxide

Part Number Type	No.	T	D	Applicable Ball	Unit Price	
					1 ~ 49 pc(s)	50-100 pcs.
CRBP	12	12	6	CRB12		
	20	22	10	CRB20		

* Product CRBP12 is shipped if the number isn't specified.

Covers for Construction Balls

CRBC

Material: SPCC
Surface Treatment: Black Oxide

Part Number Type	No.	A	(B)	C	Applicable Ball	Unit Price	
						1 ~ 49 pc(s)	50-100 pcs.
CRBC	12	25	21	25	CRB12		
	20	35	31	30	CRB20		

* Product CRBC12 is shipped if the number isn't specified.

Ordering Example: Part Number
CRB20
CRBP20
CRBC12