

Proximity Sensor Flags

Set Screw / Slit

Limit Switch Flags P2093, 2094

Set Screw

RoHS10

Part Numbers in are not RoHS compliant.

Shaft Bore	Type	M Material	S Surface Treatment	A Accessory
Disc Type with Through Hole	DSS	S45C	Black Oxide	Set Screw 2 pcs.
Disc Type with Tapped Hole	DMG, DMGFS			Set Screw 2 pcs., Brass Ball 2 pcs.

Disc Type with Through Hole and Set Screw
DSS

Disc Type with Tapped Hole and Set Screw
DMG (With Brass Ball)

Stepped Type with Tapped Hole and Set Screw
DMGFS (With Brass Ball)

With Through Hole and Set Screw

Part Number	Type	D	d	Unit Price	Volume Discount Rate
				1 ~ 9 pc(s).	10~50
DSS		25	8		
		30	10		
		40	12 16		
		50	12 16		

With Tapped Hole and Set Screw

Part Number	Type	D	M (Coarse)	Unit Price	Volume Discount Rate
				1 ~ 9 pc(s).	10~50
DMG		25	8		
		30	8 10		
		40	12 16		
		50	12 16		
DMGFS		40	12		
		50	12 16		

For orders larger than indicated quantity, please check with WOS.

For orders larger than indicated quantity, please check with WOS.

Ordering Example

Part Number	-	d, M
Type D	-	
DSS 25	-	8

Limit Switch Flags P2093, 2094

With Slit

RoHS10

Type	M Material	S Surface Treatment	A Accessory
DSG, DMS, DMSL	S45C	Black Oxide	Hex Socket Head Cap Screw 1 pc.

Disc Type with Through Hole and Slit
DSG

Disc Type with Tapped Hole and Slit
DMS

Disc Type with Tapped Hole and Slit, Deep C-bore
DMSL

Disc Type with Through Hole and Slit

Part Number	Type	D	d	M1 (Coarse)	A	X	Y	Unit Price	Volume Discount Rate
								1 ~ 9 pc(s).	10~50
DSG		30	10	M5	9.0	6	6		
		40	12 16		14.0	7	8		
		50	12 16	M6	16.5	10	10		

Disc Type with a Tapped Hole and Slit

Part Number	Type	D	M (Coarse)	M1 (Coarse)	A	X	Y	Unit Price	Volume Discount Rate
								1 ~ 9 pc(s).	10~50
DMS		30	10	M5	9.0	6	6		
		40	12 16		14.0	7	8		
		50	12 16	M6	16.5	10	10		
DMSL		50	12 16	M6	15.5	10	6		

Ordering Example

Part Number	-	d, M
Type D	-	
DSG 40	-	16
DMS 30	-	10

Example

Proximity Sensor (P2063)

For orders larger than indicated quantity, please check with WOS.