

Posts for Stands / Caps for Hollow Posts

Features: Can be used in combination with Device Stands, Stand-Up Brackets and Strut Clamps.

Posts for Stands

RoHS 10

Type		Material	Hardness	Surface Treatment
Solid	Hollow			
STN	STA	S45C Equivalent 58HRC- Case Induction Hardened (Depth 1.0 ~ 1.5)		-
STNM	STAM			Electroless Nickel Plating
MSTNM	MSTAM	S45C Equivalent		Electroless Nickel Plating
GSTNM	GSTAM	S45C Equivalent		Black Oxide
STNUG	SMSTAM	SUS304		-

⚠ Surface treatment may not be applied to ends and grooves of STNM, STAM, MSTNM, MSTAM, GSTNM, GSTAM.

(Solid)

(Hollow)
(D≥10)

Part Number		Dg6	L 1mm Increment	(D1)	l	h	(d)
Type							
Solid STN STNM MSTNM GSTNM STNUG	6	-0.004 -0.012	30~150	4.5	12	4	-
	8	-0.005	30~200	6.5	15		
	10	-0.014	35~250	8.5	18		
	12	-0.006	35~300	10	10	5	6.0
	15	-0.017	40~350	13	20		
	20	-0.007	45~400	17	25	6	10.0
	25	-0.007	50~450	22	30		
	30	-0.020	60~450	27	30	8	11.7
	35	-0.009	70~500	32	40		
	40	-0.025	80~500	37	40	10	15.2
50	-0.025	100~600	46	50			

⚠ Hollow Posts are available from D10. STN is applicable from D8.

Ordering Example: Part Number - L
STNUG12 - 250

Alterations

Part Number - L - (MN, MTC)
STN8 - 100 - MN

Alteration	Code	Spec.																						
No Groove 	MN	Alteration to No Set Screw Groove. (Ordering Code) MN																						
One End Tapped 	MTC	Tapped at one end. (Ordering Code) MTC8 <table border="1"> <thead> <tr> <th>Dg6</th> <th>M (Coarse)</th> </tr> </thead> <tbody> <tr><td>8</td><td>3</td></tr> <tr><td>10</td><td>3 4</td></tr> <tr><td>12</td><td>4 5</td></tr> <tr><td>15</td><td>4 5 6</td></tr> <tr><td>20</td><td>5 6 8</td></tr> <tr><td>25</td><td>6 8 10</td></tr> <tr><td>30</td><td>8 10 12</td></tr> <tr><td>35</td><td>10 12 16</td></tr> <tr><td>40</td><td>10 12 16</td></tr> <tr><td>50</td><td>10 12 16</td></tr> </tbody> </table> <p>⚠ Applicable to Solid Type only. ⚠ Not applicable to D=6.</p>	Dg6	M (Coarse)	8	3	10	3 4	12	4 5	15	4 5 6	20	5 6 8	25	6 8 10	30	8 10 12	35	10 12 16	40	10 12 16	50	10 12 16
Dg6	M (Coarse)																							
8	3																							
10	3 4																							
12	4 5																							
15	4 5 6																							
20	5 6 8																							
25	6 8 10																							
30	8 10 12																							
35	10 12 16																							
40	10 12 16																							
50	10 12 16																							

D	L	Unit Price									
		Solid					Hollow				
		STN	STNM	MSTNM	GSTNM	STNUG	STA	STAM	IMSTAM	GSTAM	SMSTAM
6	30~100	-									
6	101~150										
8	30~100										
8	101~200										
10	35~150										
10	151~250										
12	35~150										
12	151~300										
15	40~200										
15	201~350										
20	45~200										
20	201~400										
25	50~200										
25	201~450										
30	60~200										
30	201~450										
35	70~300										
35	301~500										
40	80~300										
40	301~500										
50	100~300										
50	301~600										

Features: Caps can be mounted on the end face of Hollow Posts on P2145-P2152.

Caps for Hollow Posts

CAP

RoHS 10

Material: Natural Rubber (NR70)

Part Number	Type	No.	D	d	d1	T	Unit Price	Volume Discount Rate
10	CAP	9	9	6.2	3	8	1 ~ 19 pc(s).	20 ~ 50 pcs.
12		11	11	6.2	3			
15		14	14	10.2	6			
20		18	18	12.0	6			
25		23	23	15.5	9			
30		28	28	16.5	10	10		
35		33	33	20.5	13			
40		38	38	23.0	15			
50		48	48	31.3	16			

⚠ For orders larger than indicated quantity, please check with WOS.

Ordering Example: Part Number
CAP25