

Comparison Points with Similar Products | Replacement Cycle (Reference) : 100,000 times Convenient package sale is available at a low price.

Double Tipped Probe
Sold by the package (50 pcs./pkg.)

RNPA028

Part	Material	Surface Treatment
(1) Plunger	SK4	Gold Plating on Nickel Undercoat
(2) Barrel	Phosphor Bronze	Gold Plating on Nickel Undercoat
(3) Spring	SUS304	Gold Plating

Double Tipped Probe
Sold by the package (50 pcs./pkg.)

RNPC028

Part	Material	Surface Treatment
(1) Plunger	BeCu	Gold Plating on Nickel Undercoat
(2) Barrel	Phosphor Bronze	Gold Plating on Nickel Undercoat
(3) Spring	SWP	Gold Plating

Double Tipped Probe
Sold by the package (50 pcs./pkg.)

RNPA030

Part	Material	Surface Treatment
(1) Plunger	BeCu	Gold Plating on Nickel Undercoat
(2) Barrel	Phosphor Bronze	Gold Plating on Nickel Undercoat
(3) Spring	SWP	Gold Plating

Part Number		Tip Shape		Mounting Pitch (min)	Full Stroke	Spring Pressure (2/3 Stroke)	Allowable Current	Resistance	Replacement Cycle (Reference)	Unit Price (50 pcs./pkg.)
Type	No.	Left Side	Right Side							
RNPA	028	B	U, B, J	0.4mm	1.1mm	20±6gf	1.0A	80mΩ	100,000 times	
		J1	U, J							
RNPC	028	B	B	0.4mm	1.0mm	12±3gf	0.5A	180mΩ	100,000 times	
RNPA	030	B	U, B, J	0.4mm	1.1mm	10±3gf	0.5A	80mΩ	100,000 times	
		J1	U, J							

Ordering Example: Part Number (Type, No.) - **L** - **R**
RNPA028 - J1 - U