

■ Straight, Chamfered

RoHS10

Type	M Material	H Hardness
MSCM	SUS440C	58HRC~
MSCSM	SUS304	-

MSCM MSCSM
(Identification Mark)

C	Part Number		L	Unit Price	Volume Discount Rate		
	Type	D			1 - 19 pc(s)	20~29	30~49
0.3 or Less	MSCM	2	6 8 10 12 15				
		3	10 12 15 20				
		4	10 12 15 20				
0.5	MSCM	5	10 12 15 20				
		6	10 12 15 20 25				

☎ For orders larger than indicated quantity, please check with WOS.

C	Part Number		L	Unit Price	Volume Discount Rate		
	Type	D			1 - 19 pc(s)	20~29	30~49
0.3 or Less	MSCSM	2	6 8 10 12 15				
		3	10 12 15 20				
		4	10 12 15 20				
0.5	MSCSM	5	10 12 15 20				
		6	10 12 15 20 25				

☎ For orders larger than indicated quantity, please check with WOS.

■ Straight - High Precision

RoHS10

Type	M Material	H Hardness
MSV	SUJ2	58HRC~
MSVC	SUS440C	58HRC~

☎ Measurement is taken place in constant temperature room.
 ☎ ℓ1, ℓ2 dimension may become larger than the value shown in the catalog due to polishing process.

ℓ1	ℓ2	Part Number		L	Unit Price	Volume Discount Rate		
		Type	D			1~49	50~499	500~2000
1	0.2	MSV	2	6 8 10				
			3	8 10 15 20 25 30				
			4	10 15 20 25 30				
0.5	1.5	MSV	5	10 15 20 25 30				
			6	10 15 20 25 30				
2	2.5	MSV	8	20 30 40				
			10	30 40 50 60				

☎ For orders of 1 ~ 9 pc(s): Unit Price + Low Quantity Surcharge (1 Line Item) ☎ For orders larger than indicated quantity, please check with WOS.

ℓ1	ℓ2	Part Number		L	Unit Price	Volume Discount Rate		
		Type	D			1~9 pc(s)	10~49	50~99
0.4	0.1	MSVC	1	5 6 8 10				
			1.5	5 6 8 10				
1	0.2	MSVC	2	5 6 8 10				
			3	6 8 10 15 20 25 30				
			4	8 10 15 20 25 30				
0.5	1.5	MSVC	5	10 15 20 25 30				
			6	10 15 20 25 30				
2	2.5	MSVC	8	20 30 40				
			10	30 40 50 60				

☎ For orders larger than indicated quantity, please check with WOS.

Ordering Example

Part Number	L
MS2	10
MSCM4	12
MSV2	6

☎ For orders larger than indicated quantity, please request a quotation. P99