

GRACE INERTIA Connector Series

Quick Reference Guide

GRACE INERTIA PRODUCT OFFERING

Centerline	Positions	Cap Housing	Plug Housing	Header Assembly	Optional TPA
3.3 mm	4P	-	1-1971905-2	1-1971906-2	1971904-2
3.3 mm	6P	-	1-1971905-3	1-1971906-3	1971904-3
3.3 mm	8P	-	1-1971905-4	1-1971906-4	1971904-4
3.3 mm	10P	-	1-1971905-5	1-1971906-5	1971904-5
3.3 mm	12P	-	1-1971905-6	1-1971906-6	1971904-2
3.5 mm	2P	2-1565085-3	2-1565081-3	-	1565089-1, 5-1565089-1
3.5 mm	2P	3-1565085-4	3-1565081-4	-	1565089-1, 5-1565089-1
3.5 mm	2P	1-1565085-2	1-1565081-2	-	1565089-1, 5-1565089-1
3.5 mm	2P	1565085-1	1565081-1	-	1565089-1, 5-1565089-1
3.5 mm	3P	2-1565086-3	2-1565082-3	-	1565090-1, 5-1565090-1
3.5 mm	3P	3-1565086-4	3-1565082-4	-	1565090-1, 5-1565090-1
3.5 mm	3P	1565086-1	1565082-1	-	1565090-1, 5-1565090-1
3.5 mm	4P	1565087-1	1565083-1	-	1565089-1, 5-1565089-1
3.5 mm	6P	1565088-1	1565084-1	-	1565090-1, 5-1565090-1
6.0 mm	2P	-	2-2232875-1	2-2232876-1	-
6.0 mm	3P	-	3-2232875-1	3-2232876-1	-
6.2 mm	1P	1903684-1	1903683-1	-	-
6.2 mm	2P	1746977-1	1746975-1	-	-
6.2 mm	3P	1746978-1	1871867-1	-	-
6.5 mm	3P	-	1747047-1	1747049-1	-
7.92 mm	2P	-	3-1747050-1	3-1747052-1	-
7.92 mm	2P	-	1747050-1	1747052-1	-
7.92 mm	2P	-	3-1747050-4	3-1747052-4	-
9.0 mm	3P	-	1-1903414-1, -2*	1-1903415-1	2232563-1
9.0 mm	3P	-	1903414-1, -2*	1903415-1	2232563-1
9.0 mm	3P	-	2-1903414-1, -2*	2-1903415-1	2232563-1
12.4 mm	2P	-	1747995-1	1747996-1	1-2232564-1
12.4 mm	2P	-	1747995-2	1747996-2	1-2232564-1
12.4 mm	2P	-	1747995-3	1747996-3	1-2232564-1

*Models with "-2" suffix on part number accommodate optional TPA.

Please note that this is only a small selection of GRACE INERTIA series products. There are a number of additional configurations available including various colors, keying options, and double lock plates where applicable. To see a complete selection of GRACE INERTIA product visit TE.com or contact your sales representative for more information.