

## ▶ CE05 Part Number

Insert Arrangement	Part Number		Backshell Style	Waterproof Cable Clamp or Conduit
	Receptacle	Plug		
10SL-3	CE05-2A10SL-3PC-D	CE05-6A10SL-3SC-D(R1)	Without Backshell	Conduit
		CE05-6A10SL-3SC-D-BSS(R1)	Straight Backshell	CE3057-4A-1-D(R1)
		CE05-8A10SL-3SC-D-BAS(R1)	Angle Backshell	
14S-2	CE05-2A14S-2PD-D	CE05-6A14S-2SD-D(R1)	Without Backshell	Conduit
		CE05-6A14S-2SD-D-BSS(R1)	Straight Backshell	CE3057-6A-1-D(R1)
18-10	CE05-2A18-10PD-D	CE05-6A18-10SD-D(R1)	Without Backshell	Conduit
		CE05-6A18-10SD-D-BSS(R1)	Straight Backshell	CE3057-10A-□-D(R1)
		CE05-8A18-10SD-D-BAS(R1)	Angle Backshell	
	CE05-2A18-10SD-D	CE05-6A18-10PD-D(R1)	Without Backshell	Conduit
		CE05-6A18-10PD-D-BSS(R1)	Straight Backshell	CE3057-10A-□-D(R1)
		CE05-8A18-10PD-D-BAS(R1)	Angle Backshell	
18-12	CE05-2A18-12PD-D	CE05-6A18-12SD-D(R1)	Without Backshell	Conduit
		CE05-6A18-12SD-D-BSS(R1)	Straight Backshell	CE3057-10A-□-D(R1)
		CE05-8A18-12SD-D-BAS(R1)	Angle Backshell	
20-4	CE05-2A20-4PD-D	CE05-6A20-4SD-D(R1)	Without Backshell	Conduit
		CE05-6A20-4SD-D-BSS(R1)	Straight Backshell	CE3057-12A-□-D(R1)
		CE05-8A20-4SD-D-BAS(R1)	Angle Backshell	
	CE05-2A20-4SD-D	CE05-6A20-4PD-D(R1)	Without Backshell	Conduit
		CE05-6A20-4PD-D-BSS(R1)	Straight Backshell	CE3057-12A-□-D(R1)
		CE05-8A20-4PD-D-BAS(R1)	Angle Backshell	
20-15	CE05-2A20-15PD-D	CE05-6A20-15SD-D(R1)	Without Backshell	Conduit
		CE05-6A20-15SD-D-BSS(R1)	Straight Backshell	CE3057-12A-□-D(R1)
		CE05-8A20-15SD-D-BAS(R1)	Angle Backshell	
	CE05-2A20-15SD-D	CE05-6A20-15PD-D(R1)	Without Backshell	Conduit
		CE05-6A20-15PD-D-BSS(R1)	Straight Backshell	CE3057-12A-□-D(R1)
		CE05-8A20-15PD-D-BAS(R1)	Angle Backshell	
20-18	CE05-2A20-18PDE-D	CE05-6A20-18SDE-D(R1)	Without Backshell	Conduit
		CE05-6A20-18SDE-D-BSS(R1)	Straight Backshell	CE3057-12A-□-D(R1)
		CE05-8A20-18SDE-D-BAS(R1)	Angle Backshell	
22-22	CE05-2A22-22PD-D	CE05-6A22-22SD-D(R1)	Without Backshell	Conduit
		CE05-6A22-22SD-D-BSS(R1)	Straight Backshell	CE3057-12A-□-D(R1)
		CE05-8A22-22SD-D-BAS(R1)	Angle Backshell	
	CE05-2A22-22SD-D	CE05-6A22-22PD-D(R1)	Without Backshell	Conduit
		CE05-6A22-22PD-D-BSS(R1)	Straight Backshell	CE3057-12A-□-D(R1)
		CE05-8A22-22PD-D-BAS(R1)	Angle Backshell	
22-23	CE05-2A22-23PD-D	CE05-6A22-23SD-D(R1)	Without Backshell	Conduit
		CE05-6A22-23SD-D-BSS(R1)	Straight Backshell	CE3057-12A-□-D(R1)
		CE05-8A22-23SD-D-BAS(R1)	Angle Backshell	
	CE05-2A22-23SD-D	CE05-6A22-23PD-D(R1)	Without Backshell	Conduit
		CE05-6A22-23PD-D-BSS(R1)	Straight Backshell	CE3057-12A-□-D(R1)
		CE05-8A22-23PD-D-BAS(R1)	Angle Backshell	
24-10(D)	CE05-2A24-10PD-D	CE05-6A24-10SD-D(R1)	Without Backshell	Conduit
		CE05-6A24-10SD-D-BSS(R1)	Straight Backshell	CE3057-16A-□-D(R1)
		CE05-8A24-10SD-D-BAS(R1)	Angle Backshell	
24-10(G)	CE05-2A24-10PG-D	CE05-6A24-10SG-D(R1)	Without Backshell	Conduit
		CE05-6A24-10SG-D-BSS(R1)	Straight Backshell	CE3057-16A-□-D(R1)
		CE05-8A24-10SG-D-BAS(R1)	Angle Backshell	
24-11	CE05-2A24-11PGH-D	CE05-6A24-11SGH-D(R1)	Without Backshell	Conduit
		CE05-6A24-11SGH-D-BSS(R1)	Straight Backshell	CE3057-16A-□-D(R1)
		CE05-8A24-11SGH-D-BAS(R1)	Angle Backshell	
32-17	CE05-2A32-17PD-D	CE05-6A32-17SD-D(R1)	Without Backshell	Conduit
		CE05-6A32-17SD-D-BSS(R1)	Straight Backshell	CE3057-20A-□-D(R1)
		CE05-8A32-17SD-D-BAS(R1)	Angle Backshell	
	CE05-2A32-17SD-D	CE05-6A32-17PD-D(R1)	Without Backshell	Conduit
		CE05-6A32-17PD-D-BSS(R1)	Straight Backshell	CE3057-20A-□-D(R1)
		CE05-8A32-17PD-D-BAS(R1)	Angle Backshell	

\*If you use the conduit, please ask conduit supplier.